

EMERGENCY ENCLOSURES

PRODUCT TYPE:

Insulating containers for electric equipment

APPLICATIONS:

Wall mounted



DIMENSIONS AND POWER DISSIPATION:

Product Name	External Dimensions in mm (LxHxD)	Number of modules/rows	Power dissipation
IP55 CE PULS R	120x120x61	Push-button socket	-
IP65 CE 04 D22 R	128x195x103	Push-button socket	-
IP65 CE 04 R	128x195x103	4 / 1	12 W
IP65 CE 04 GRI	128x195x103	4 / 1	12 W
IP65 CE 08 R	200x195x106	8 / 1	18 W
IP65 CE 08 GRI	200x195x106	8 / 1	18 W
IP65 CE 08 PDF R	200x195x106	Back plate	18 W
IP55 CE 04 INC R	150x195x101	4 / 1	15 W
IP55 CE 04 INC GRI	150x195x101	4 / 1	15 W

COLOUR RANGE:

Red RAL 3000 – Grey RAL 7035

MATERIALS:

- **Casing:** ABS, ABS/PC, PS (recessed model back plate) – (Halogen Free)
- **Door:** ABS, ABS/PC + Glass (Halogen Free)

DECLARATION OF CONFORMITY:

All Pablo range products come under the scope of the Low Voltage Directive 2014/35/UE and comply with all relevant essential requirements set in the Directive.

Compliance with the Directive is indicated by the **CE** marking and by all required symbols and markings affixed on the product, its packaging, in the assembly instructions and product catalogue, as well as by full product compliance with applicable standards.

NORMATIVE REFERENCES:

- EN 60670-1: "Boxes and enclosures for electrical accessories for household and similar fixed electrical installations - Part 1: General requirements"
- EN 60670-24: "Boxes and enclosures for electrical accessories for household and similar fixed electrical installations - Part 24: Particular requirements for enclosures for housing protective devices and other power dissipating electrical equipment"

Degree of protection provided by Enclosures as per EN 60529 standard "Degrees of protection provided by enclosures (IP Code)": IP55/IP65

Resistance to impact as per EN 62262 Standard "Degrees of protection provided by enclosures for electrical equipment against external mechanical impacts (IK Code)": IK08 (5 Joules)

Resistance to hot-wire based test as per EN 60695-2-11 Standard "Fire hazard testing – Part 2-11: Glowing/hot-wire based test methods – Glow-wire flammability test method for end-products": passed the 650 °C test.

Electric insulation (EN 61439-1): products feature full insulation components for protection against indirect contact (Class II). However, in order to ensure protection, they must be correctly installed according to the instructions provided by the manufacturer and using the appropriate accessories (e.g. screw caps, clamps).

MINIMUM INSTALLATION AND SERVICE TEMPERATURE:

-25 °C

MAXIMUM SERVICE TEMPERATURE:

+60 °C

ELECTRICAL INSULATING PROPERTIES:

yes (rated voltage up to 1000 V AC)

RESISTANCE TO CHEMICAL AGENTS:

	Saline	Acids		Bases		Solvents				Mineral Oil
		Concentrated	Thinned	Concentrated	Thinned	Hexane	Benzoic acid	Acetone	Ethyl-alcohol	
	Resistant	Unsuitable	Resistant	Resistant	Resistant	Resistant in certain conditions	Unsuitable	Unsuitable	Resistant in certain conditions	Resistant in certain conditions

CONFORMITY WITH 2011/65/CE (ROHS) DIRECTIVE:

yes

