

AENOR

AENOR Product Certificate Low Voltage Material



030/002068

AENOR certifies that the organization

HAGER ELECTRO, SAS

registered office 132, BOULEVARD D'EUROPE 67210 OBERNAI CEDEX (Francia)

supplies Circuit-Breakers for overcurrent protection for household and similar installation

in compliance with UNE-EN 60898-1:2004 (EN 60898-1:2003; EN 60898-1:2003 CORR:2004)
UNE-EN 60898-1:2004/A11:2006 (EN 60898-1:2003/A11:2005)
UNE-EN 60898-1:2004/A1:2005 (EN 60898-1:2003/A1:2004)
UNE-EN 60898-1:2004/A12:2009 (EN 60898-1:2003/A12:2008)
UNE-EN 60898-1:2004/A13:2013 (EN 60898-1:2003/A13:2012)

References Specified in Annex to the Certificate

Production site N. 5 HE CHANG DONG SI ROAD. ZHONGKAI HIGH-TECH INDUSTRIAL DEVELOPMENT ZONE HUIZHOU CITY (516006 Guangdong - China)

Certification scheme In order to grant this Certificate, AENOR has tested the product and has verified the quality system implemented for its manufacture. AENOR performs these tasks periodically while the Certificate has not been cancelled, in accordance with Specific Rules RP 030.15.

This certificate supersedes 030/002068, dated 2015-02-25

First issued on 2007-08-31
Modified on 2017-09-11
Validity date 2022-09-11

Rafael GARCÍA MEIRO
Chief Executive Officer

Original Electrónico

AENOR

AENOR Product Certificate Low Voltage Material

030/002068

Annex to Certificate

Trade mark: HAGER

Type Ref.	No. of poles	Rated voltage	Rated current	Short circuit capacity	Individual pole capacity	Energy limiting class	Tripping current
MN906V	1P+N	230 V-	6 A	6000 A	6000 A	3	C
MN910V	1P+N	230 V-	10 A	6000 A	6000 A	3	C
MN916V	1P+N	230 V-	16 A	6000 A	6000 A	3	C
MN920V	1P+N	230 V-	20 A	6000 A	6000 A	3	C
MN925V	1P+N	230 V-	25 A	6000 A	6000 A	3	C
MN932V	1P+N	230 V-	32 A	6000 A	6000 A	3	C

First issued on 2007-08-31
Modified on 2017-09-11
Validity date 2022-09-11

Original Electrónico

AENOR INTERNACIONAL S.A.U.
Génova, 6. 28004 Madrid. España
Tel. 91 432 60 00.- www.aenor.com