# :hager

E

easylink

5

# 

# **TXE530**

Weather station with GPS

# Safety instructions


Electrical equipment may only be installed and assembled by a qualified electrician. Always follow the relevant accident prevention regula-

Failure to comply with these installation instructions may result in damage to the device, fire or other hazards.

When installing and laying cables, always comply with the applicable regulations and standards for SELV electrical circuits.

These instructions are an integral component of the product and must be retained by the end

Design and layout of the device



- Figure 1: Exterior view
- (1) Precipitation sensor on housing cover
- (2) Brightness/twilight sensor
- (3) Housing, bottom part
- (4) Temperature sensor
- (5) Wind sensor

## Function

#### System information

This device is a product of the KNX system and corresponds to the KNX guidelines. Detailed specialised knowledge obtained from KNX training courses

is required for understanding. The planning, installation and commissioning are carried out with the help of KNX-certified software.

#### Systemlink start-up

The function of the device is software-dependent. The software is to be taken from the product database. You can find the latest version of the product database, technical descriptions as well as conversion and additional support programmes on our website.

#### Easylink start-up

The function of the device is configuration-dependent. The configuration can also be done using devices developed specially for simple setting and start-up.

This type of configuration is only possible with GB devices of the easylink system. Easylink stands for easy, visually supported start-up. Preconfigured standard functions are assigned to the in/outputs by means of a service module

> During Easylink start-up, only one weather station can be configured per installation.

#### Correct use

- Measurement and evaluation of the weather data: precipitation, temperature, wind speed, twilight and brightness
- Horizontal installation on the outside of buildings (figure 3), preferably in the roof and facade
- The measured values apply to the installation U location. Variations to other weather services-e.g. through local turbulence or areas with build-ups of air – are possible

#### Product characteristics

- Integrated KNX bus coupling and data processing unit
- Integrated GPS antenna
- Direct control of switching outputs via alarm stages: rain alarm, frost alarm, wind alarm in 3 stages - 4, 8 or 12 m/s.
- Reception of date, time and location data (installation location) via GPS signal
- convenient shade and heat protection functions (with position tracking and horizontal sun tracking) for up to four building facades through the use of a brightness sensor and accurate solar positioning calculations
- By integrating the weather station into the domovea visualisation, you can access enhanced functions such as setpoint settings for controlling switching outputs, logic functions and the timer

#### GPS data, date, time

The date time and exact location coordinates of the weather station are received via the GPS signal. Date and time can also be received via the KNX bus and may be used as master or slave depending on ETS programming.

This information is required to control the automatic changeover for daylight savings time.

- If programmed, the device receives the date and time during first start-up via the KNX bus until the first GPS signal is received.
- If the device is operated in a country that does not require changes to be made for daylight savings time, the Summer time offset in minutes should be set to zero ...

#### Maintaining the device

The weather station should be checked for soiling at regular intervals – at least twice a year – and cleaned if necessary

- Heavy soiling can make it impossible to calcu-Iate wind speed correctly, cause the precipitation sensor (1) to display a permanent precipita-
- tion message, or prevent the brightness sensor (2) from detecting any sunlight.

# Scope of delivery

- Weather station Wall/mast fixing
- Set of screws and dowels for wall mounting
- 2 Cable ties for mast assembly
- U the device in a direction other than south to accommodate existing walls or other geographical factors.
- Use a spirit level to align the device horizontally (figure 3).

### Information for electricians

#### Installation and electrical connection

DANGER!


**C** Touching live parts in the installation environment can result in an electric shock.

> The device could get damaged. Disconnect the connecting cables before working on the device and cover all live parts in the area!

#### Selecting installation location

Select the assembly location so that wind, precipitation and sun can be detected by the sensors without impedance:

- Avoid influences by obstacles or shadings such as facades, roofs or trees
- Do not install underneath construction components that can delay precipitation from reaching the sensor
- Avoid influences on the GPS signal caused by magnetic fields, transmitters and interference fields for electrical devices, such as fluorescent lamps, neon signs and switching power supply
- Do not mount in the vicinity of chimneys or other gas or ventilation systems
- Do not mount in the vicinity of radio transmitter systems
- Leave a minimum distance to surfaces below the weather station of 60 cm in order to guarantee correct measurement of wind and in order to not get snowed in
- Install on vertical walls (figure 2) or on a mast (figure 5, right)
- Select the mounting location so that the weather station will always be accessible for maintenance purposes.



# Figure 2

#### Alianina the device

To measure the brightness accurately, align the weather station in such way that the brightness/ twilight sensor (2) faces south.

• Use a compass to align the device to the south (figure 3).

An incorrect alignment may influence the measured values of the brightness sensor.

- In some cases, it may be appropriate to align




Figure 3: Aligning the device horizontally and to face south

# Connecting and installing the device

Bobserve the layout requirements for SELV installations.

Cables parallel to mains cables.

The weather station is supplied complete with a wall/mast fixing (6). This is locked into place on the rear of the device upon delivery (figure 4).

- device on walls, masts or brackets (see accessories)
- Carefully loosen the wall/mast fixing (6) from the detent mechanism using a screwdriver and slide it downwards to remove (figure 4).



- Figure 4: Loosening the wall/mast fixing


When doing so, please ensure that:

- In the case of wall mounting, the smooth side lies against the wall and the crescent-shaped
- bar (7) is at the top (figure 5, left). In the case of mast mounting, the curved side lies against the mast and the crescent-shaped bar (7) is at the bottom (figure 5, right). The distance between the holes and the meas-U urements for aligning them can be found in the


- accompanying drilling plan.

(6) Wall/mast fixing

• Use two screws to attach the fixing vertically to a wall or use the accompanying cable ties to attach it to a mast.



- To avoid EMC interference, do not install input
- Optional holders are available for mounting the








Figure 5: Wall fixing (left) or mast fixing (right) (7) crescent-shaped ba

- Gently pull the cover apart from the detent mechanisms (9) at the sides and remove the cover (8) from the bottom part of the housing
- Take care when opening the weather station. The precipitation sensor in the cover and the printed circuit board in the bottom part of the housing are connected by a cable.



#### Figure 6: Preparation for mounting

- (8) Cover with precipitation sensor
- (9) Detent mechanisms on the cover
- Route the cables from the auxiliary voltage and KNX bus through the rubber seals on the bottom part of the weather station.
- bus coupling unit may be used for connection of auxiliary voltage.
- nal (11). Be sure that the polarity is correct.
- nals (10).



- Figure 7: Interior view
- (10) Connecting terminals for auxiliary voltage
- (11) KNX bus connection terminal
- (12) Connector for precipitation sensor in the housing cove (13) Programming button and programming LED
- (14) GPS antenna
- Place cover (8) onto the bottom part of the housing (3) and push carefully until it engages audibly
- Slide the weather station into the mounted fixing from above. Ensure that the pins for the wall/mast fixing engage audibly into the guides for the bottom part of the housing (figure 8).
- The weather station is ready for operation.
- The wind measured value and all wind switching outputs cannot be outputted until 60 seconds after the auxiliary voltage has been applied




Figure 8: Installing onto the fixing

In the event of any damage, take the device out of operation immediately and safeguard against turning back on.

- Opening the device may allow moisture to enter the interior.
- electronics.

Do not open the device in the event of precipitation and be sure to remove any external moisture from the device with a dry cloth before attempting to disassemble.

- Pull upwards against the resistance created by the detent mechanism to remove the device from the wall/mast fixing from above.
- Gently pull the cover apart from the detent mechanisms (9) at the sides and remove the cover (8) from the bottom part of the housing

Disconnect bus line (11) and auxiliary voltage

#### Start-up

The weather station must only be operated from Its fixed installation position once all installation and commissioning work is complete. Systemlink – Loading the physical address and

# application software

The device is mounted and also connected to the KNX bus and auxiliary voltage.

- It is advisable to program the physical address before installation.
- The physical address is only ever assigned for one device. Only one device can ever be in programming mode.
- Gently pull the cover apart from the detent mechanisms (9) at the sides and remove the cover (8) from the bottom part of the housing
- Take care when opening the weather station.
- The precipitation sensor in the cover and the printed circuit board in the bottom part of the housing are connected by a cable.
- Switch on bus voltage • Switch on auxiliary voltage.
- Press programming button (13). The programming LED (13) lights up.
- If the programming LED does not light up, no bus voltage is present.
- Load the physical address into the device. The programming LED (13) goes out
- Load application software Note down the physical address on the labelling field.
- The loading of non-compatible application software is indicated by flashing of the programming LED (13)
- Place cover (8) onto the bottom part of the housing (3) and push carefully until it engages audibly
- The weather station has been commissioned.

#### Easylink

Information on the system configuration can be taken from the extensive description of the service module easylink.

During Easylink start-up, only one weather Station can be configured per installation.

## Appendix

**Technical data** 

	rechnical data		
	KNX Medium		TP 1
	Configuration mode	S-I	Node, E-Controller
	Rated voltage KNX		30 V SELV
	Current consumption KNX		max. 6 mA
l	Connection mode KNX	bus c	onnecting terminal
	Auxiliary voltage		<del></del> 12 40 V SELV ~ 12 24 V SELV
	Auxiliary current		185 mA at 12 V <del></del> . 80 mA at 24 V <del></del>
	Operating temperature		-30 + 50 °C
	Operating altitude		max. 2000 m
	Storage/transport temperat	ture	-30 +70 °C
	Conductor cross-section (r	igid)	max. 0.5 mm <sup>2</sup>
	Dimensions (W x H x D)	ca.	96 x 77 x 118 mm
	Weight		170 g
	Degree of protection		IP44
	Surge voltage		1500 V
	Overvoltage category		III
	Degree of contamination		2

oftware	class A			
tion type	type 2			
all test temperature	75 °C			
ecipitation sensor: Aeasurement precipitat Heating	tion Yes/No (1 bit) approx. 1.2 W			
mperature sensor: Measuring range Resolution Measuring accuracy	-30 +80°C 0.1 °C ± 0,5 °C at +10 +50 °C ± 1 °C at -10 +85 °C ± 1,5 °C at -25 +150 °C			
ind sensor: Measuring range Resolution Measuring accuracy	0 35 m/s 0.1 m/s ± 15% of measured value			
th an incidental flow from 90 $\dots$ 270 $^\circ$				
ightness/twilight senso Cardinal direction Measuring range Measuring accuracy	r South 0 lx 150 klx ± 20 % at 0 lx 10 klx			

Cardinal direction	South
Measuring range	0 lx 150 klx
Measuring accuracy	± 20 % at 0 lx 10 klx
	± 15 % at 10 … 150 klx
est mark	KNX, CE
, 0	EMC Directive 2004/108/ age Directive 2006/95/EC
tandards	EN 50491-3
	EN 50491- 5 -2: 2011
	EN 60730 - 1: 2011

## Troubleshooting

#### Bus operation is not possible

Cause 1: Bus voltage is not present. Check bus connection terminals (11) for correct

Cause 2: Auxiliary voltage is not present. Check connection for auxiliary voltage (10).

Check auxiliary voltage by means of measuring device

Auxiliary voltage is also essential for bus opera-

#### Precipitation sensor is permanently covered in snowy weather


Cause: Heating does not work. Auxiliary voltage is not present.

Check connection for auxiliary voltage (10).

Check auxiliary voltage by means of measuring device.

#### Accessories

KNX power supply 320 mA + 24 V DC, 640 mA RMD	TXA114
Power supply flush-mounted, 24 V DC auxiliary voltage)	TP110
Hinge arm, arge, for weather station KNX	TG353
linge arm, mall, for weather station KNX	TG354



- The second wire pair (yellow/white) of the KNX
- · Connect the bus cable via the connecting termi-
- - · Connect auxiliary voltage to connecting termi-

- Dismantling the device CAUTION!
- This would result in damage to the

2