







ZAL53UE, ZAL64UE, ZAL83UE, ZAL84UE, ZAL85UE

- (EN) Mounting instructions
(FR) Notice d'instructions
(DE) Montageanleitung
(NL) Montage instructie
(DA) Monteringsvejledning
(FI) Asennusohje
(NO) Montasjeanvisning
(SV) Monterings instruktioner
(IT) Istruzioni di montaggio
(ES) Instrucciones de montaje
(PT) Instruções de montagem
(CS) Montážní návod
(BS) Uputstvo za montažu
(UK) Інструкції з установки


- (HR) Upute za montažu
(HU) Szerelési útmutató
(LT) Montavimo instrukcija
(LV) Montāžas instrukcija
(PL) Instrukcja montażowa
(RO) Instrucțiuni de montare
(SK) Návod na montáž
(RU) Указания по установке
(BG) Инструкции за монтаж
(EL) Οδηγίες τοποθέτησης
(SL) Navodilo za montažo
(EE) Paigaldusjuhised
(IS) Leiðbeiningar
(AR) دليل التركيب










	a [mm]	b [mm]	c [mm]
ZAL53UE	1080	785	
ZAL83UE	1350		
ZAL64UE	1080	1115	320
ZAL84UE	1350		
ZAL85UE	1350	1445	




ZAL53UE	ZAX006E	ZAX015E	ZAX012E
ZAL83UE			
ZAL64UE	ZAX007E	ZAX016E	ZAX013E
ZAL84UE			
ZAL85UE	ZAX103E	ZAX203E	-




ZAX012E / ZAX013E






ZAL83UE + ZAX006E/ ZAX015E


01



02



01



02

