


Consumer Unit Design 10 Dual Row Switch Disconnecter

For the distribution of power in a domestic application, conforming to BS EN 61439-3 including Annex ZB (16kA rating).

Design 10 dual row consumer unit is an entry level board designed for all applications and allows when fitted with RCBOs on outgoing circuits compliance with BS 7671:2008 regulations; 411.3.3 additional protection by means of a 30mA RCD, 314.1&2 segregation of circuits to avoid danger and minimise inconvenience in the event of a fault, 522.6.202 protection of wiring concealed in walls or partitions.

Metal enclosure manufactured to allow compliance with BS 7671 regulation 421.1.201



VML11414

Description	Size	Cat ref.
6+6 Way 100A Switch Disconnecter Dual Row	3 (2)	VML10606
10+10 Way 100A Switch Disconnecter Dual Row	4 (2)	VML11010
14+14 Way 100A Switch Disconnecter Dual Row	5 (2)	VML11414
20+20 Way 100A Switch Disconnecter Dual Row	7 (2)	VML12020

Devices	
Single Pole, Single Mod RCBO 6kA, 6A - 50A	ADN***
Single Pole, Single Mod Reduced Height RCBO 6kA, 6A - 32A	ADA3**G

Features & Benefits

- Provides for large quantities of outgoing ways or space for additional devices
- Enclosure fully open between rows giving easy access for cables
- Square cable entry points top and bottom for use with cable trunking
- Meter tail cable entry plate (VM04CE) provided
- Rigid top wall – Enhances rigidity to prevent distortion when removing knockouts
- Rear Knockouts for ease of cable entry - cable protector plate (VM02CE) available as accessory
- Front cover retained screws – Prevents loss during installation
- Full metal DIN rail – Secure and stable attachment of devices
- Quick release clip on MCB – Allows removal of MCB with busbar still in place
- Optimised cabling space – DIN rail position allows maximum cabling space
- Top mounted terminal rail for each row makes the wiring of the neutral and earth connections neat and simple.
- Torque settings displayed inside front cover – easily accessible to electrician during installation and maintenance.

Technical Characteristics

Standards	BS EN 61439-3
Classification	Consumer Unit
Rated & Operational Voltage (U_N/U_e)	230V a.c 50 Hz
Rated Insulation Voltage (U_i)	320V a.c. 50Hz
Rated Frequency (fn)	50 Hz
Rated impulse withstand voltage (U_{imp})	4kV
Rated Current of the Assembly (I_{na})	63A/100A
Rated Current of an Outgoing Circuit I_{nC}	RCBO 6A-50A (Marked Rated Current on Device)
Rated Conditional Short Circuit of the Assembly (I_{cc})	Annex ZB: 16kA rms at 250V, power factor 0.6 with equipment and arrangements specified in Hager's technical documentation/catalogue
Protection against electric shock	Consumer Unit shall be installed in an electrical system conforming to IEC 60364 / BS 7671
Rated Diversity Factor (RDF) / Values of assumed loading	10 Way and above - 0.5
Note: RDF only applies to continuously and simultaneously loaded circuits. In principle, this means adjacent circuit breakers having a load on time exceeding 30 minutes or where a load not exceeding 30 minutes has an 'off' time less than the 'on' time will need to have the rated diversity factor applied as indicated.	
Pollution Degree	2
Types of System Earthing for which the assembly is designed	TNC-S and TN-S when installed in an electrical system conforming to BS 7671
Intended locations	Indoor use only
Stationary assembly	
Degree of protection	IP2XC with door open / closed and full compliment of devices / blanks fitted. Note: Where cables are installed through the top wall of the enclosure, gaps of IP4X to be maintained.
Intended use	Intended for use in domestic (residential) or similar premises
Electromagnetic compatibility (EMC) classification	EMC environment B
External design	Wall mounted, surface type, enclosed assembly.
Mechanical impact protection	IK05
Type of construction	Fixed parts
Incoming Line/Neutral terminal (80 - 100A board)	50mm ²
Incoming Line/Neutral terminal (63A board)	25mm ²
Incoming Earth Terminal	16mm ²

Warranty - Hager undertakes to replace or repair at its discretion products should they become inoperable within the time periods as stated - 2 Years

Accessories

Top Wall cable entry plates	Provide more options for cable entry, when used with 50x50mm trunking IP ratings can be achieved.	VM03CE
Blind cable entry plates	A blank plate for drilling which allows the installer to decide on the method of incoming cables - compression gland etc.	VM04CB, VM03CB
Rear cable entry plate	Provides protection for cables entering from the rear of the board	VM02CE
Cable Clamp	Secures supply cables on entry to main incoming device	VA10MT
Grommet strip	For protecting cables against damage when entering the board	VM05GS
Rear stand off plates	To stand consumer unit off wall allowing surface mounted cables to enter through rear of unit.	VM01SP

Dual Row Design 10 Dimensions (mm)

	Enclosure Size				
	3 (2)	4 (2)	5 (2)	6 (2)	7 (2)
Height	486	486	486	486	486
Width	227	299	370	406	478
Depth 1	83	83	83	83	83
Depth 2	100	100	100	100	100

		Number of Knockouts				
☐	Top Face 30 x 25 (mm)	2	2	2	2	2
☐	Top Face 40 x 30 (mm)	2	4	4	6	6
☐	Back 100 x 50 (mm)	2	2	6	6	6
☐	Bottom Face 30 x 25 (mm)	3	4	4	5	5

