


Product Environmental Profile

13A 2 Gang Double Pole Switched Socket USB C+C PD



Company information

Hager

132 Boulevard d'Europe
F 67215 Obernai Cedex
www.hagergroup.com

A question concerning the Product Environmental Profile:
infopep@hager.com

References covered

WMSS82G-USBCC, WRSS82BSB-USBCC, WRSS82BSW-USBCC, WRSS82PSB-USBCC, WRSS82PSW-USBCC, WFSS82BSB-USBCC, WFSS82BSW-USBCC, WFSS82PSB-USBCC, WFSS82PSW-USBCC, WPSS82-USBCC, WPSS82B-USBCC, WPSS82BKO-USBCC, WPSS82W-USBCC

Methodology

PEP has been performed according to the PCR version PEP-PCR-ed4-2021 09 06 and PSR version PSR-0005-ed3-2023 06 06 issued by the PEP ecopassport program.

For further information, please see the website of the program www.pep-ecopassport.org

Reference product

Reference product identification

WMSS82-USBCC

Use scenario based on :
PSR product Category : PSR-0005-ed3-2023 06 06
Combinations of functions

Functional unit

Connect/disconnect the plug of a load consuming 13A maximum under a voltage of 230V while protecting the user from direct contact with live parts, in the Household/Commercial application areas, and provide one or more USB connection type charging point(s) USB PD 27W,5.0V /3.0A,9.0V /3.0A,12.0V /2.25A, according to the appropriate use scenario, and for the reference service life of the product of 10 years.

The functional unit is based on the use scenario recommended by the PCR for the category of the reference product.

Materials and substances

All useful measures have been adopted to ensure that the materials used in the composition of the product do not contain any substances banned by the legislation in force at the time of marketing.

Plastics			Metals			Others		
	g	%		g	%		g	%
PC	16.53	6.4%	Copper	29.22	11.3%	Urea	83.86	32.4%
ABS	16.43	6.3%	Ferrites	12.62	4.9%	Cardboard	27.72	10.7%
PA6	4.48	1.7%	Steel	21.24	8.2%	Wood	6.15	2.4%
PE-LD	4.21	1.6%	Bronze	3.98	1.5%	Glass	3.93	1.5%
Epoxy resin	2.28	0.9%	Zinc	3.94	1.5%	Melamine cyanurate	3.65	1.4%
Other	3.86	1.5%	Other	7.61	2.9%	Other	7.27	2.8%
Total mass of reference product with raw material packaging :			258.97	g				
Total mass of reference product (Product + packaging)			245.98	g				

System Boudaries

The environmental information included in the PEP covers all the stages of the life cycle, from "cradle to grave".

Manufacturing			Distribution	Installation	Use							End of life				Module D
Raw material extraction and processing	Transport to the manufacturer	Manufacturing	Distribution to the place of operation	Installation on the place of operation	Use or application of the product installed	Maintenance	Repair	Replacement	Restoration	Energy requirements during the use stage	Water requirements during the use stage	Deinstallation	Transport to the waste treatment site	Treatment of waste in view of its reuse, recovery and/or recycling	Disposal	Benefits and loads beyond the system boundaries
A1	A2	A3	A4	A5	B1	B2	B3	B4	B5	B6	B7	C1	C2	C3	C4	D
Life cycle stages																

Manufacturing

These products are manufactured by a site that has received an environmental certification ISO 14001.

This phase takes into account raw materials, manufacturing processes, production offcuts and their end-of-life treatment, upstream transport of materials and sub-assemblies to the manufacturing site, and transport from the manufacturing site to the final logistics platform.

Distribution

The packaging has been designed in accordance with current regulations. In particular, the European directive 94/62/CE relative to packaging and packaging waste.

The used packaging is 100% recyclable or recoverable. Packaging and logistic flows are continuously improved in order to reduce their impact.

This phase taken into account the transport of the finished product, including packaging, to its place of use.

Installation

Installation processes

The processes to install the product are not considered in this study because of their weak impact compared to the other life cycles steps.

This phase only take into account the impact of the the packaging waste treatment is taken into account.

Installation elements (non delivered with the product)

Elements non delivered with the product and needed to install the product are not considered.

Use

Power loss / load dependent			
Active mode		Inactive mode	
Watt	% of time	Watt	% of time
0.0185	30%	0	70%

Power consumption / not load dependent					
Active Sleep phase		Passive Sleep phase		Turn off phase	
Watt	% of time	Watt	% of time	Watt	% of time
0.9275	30%	0.04	70%	0	0%

This corresponds to a total energy consumption of 27.31 kWh for the use span of 10 years.

Energy model of the use phase :

United Kingdom

Consumables and maintenance :

None

End of life

Considering the complexity of the recycling channels for electric and electronic equipment impacts, we rely mainly on ESR modules (datasets for WEEE product end of life).

The recycling potential of the product is: 33%. The calculation of this rate is based on the method of the IEC/TR 62635.

Environmental impacts

Evaluation of the environmental impact covers the following life cycle stages: raw materials + manufacturing (RMM), distribution (D), installation (I), use (U) and end of life (EoL).

All calculations are done with EIME software version 6.2.1-17 with the database version CODDE© 2024-04 .

Indicators set : Indicators for PEF EF 3.1 (Compliance: PEP ed.4, EN15804+A2) v1.0

PEP representative of the covered products marketed in: United Kingdom

Energy models considered for each phase

Manufacturing A1-A3	Distribution A4	Installation A5	Use B1-B7	End Of Life C1-C4
China	-	United Kingdom	United Kingdom	United Kingdom

Environmental impact indicators

Indicators	Unit	Manufacturing A1-A3	Distribution A4	Installation A5	Use B1-B7	End Of Life C1-C4	GLOBAL	Module D
Acidification (PEF-AP)	mole H+ eq	2.55E-02	3.46E-03	8.39E-05	3.62E-02	2.75E-03	6.80E-02	-2.43E-02
Climate change - Total (PEF-GWP)	kg CO2 eq.	2.36E+00	7.43E-02	3.69E-02	6.82E+00	3.35E-01	9.63E+00	-1.73E-01
Climate change-Biogenic (PEF-GWPb)	kg CO2 eq.	-2.11E-02	0.00E+00	6.09E-03	2.11E-02	5.34E-02	5.94E-02	-3.87E-03
Climate change-Fossil (PEF-GWPf)	kg CO2 eq.	2.38E+00	7.43E-02	3.09E-02	6.79E+00	2.82E-01	9.57E+00	-1.69E-01
Climate change-Land use and land use change (PEF-GWPlu)	kg CO2 eq.	2.56E-05	0.00E+00	0.00E+00	0.00E+00	0.00E+00	2.56E-05	0.00E+00
Ecotoxicity, freshwater (PEF-CTUe)	CTUe	1.89E+02	4.43E-02	3.82E-01	1.88E+01	3.80E+00	2.12E+02	-3.92E+00
EF-particulate Matter (PEF-PM)	Incidence of diseases	1.37E-07	1.36E-08	4.67E-10	3.00E-07	6.14E-09	4.57E-07	-3.28E-08
Eutrophication, freshwater (PEF-Epf)	kg P eq.	8.21E-05	2.55E-08	3.85E-07	2.01E-05	2.40E-06	1.05E-04	-1.55E-03
Eutrophication marine (PEF-Epm)	kg N eq.	2.22E-03	6.08E-04	3.56E-05	4.17E-03	1.15E-03	8.19E-03	-7.25E-04
Eutrophication, terrestrial (PEF-Ept)	mole of N eq.	2.38E-02	6.66E-03	2.27E-04	1.13E-01	1.75E-03	1.46E-01	-9.23E-03
Human toxicity, cancer (PEF-CTUh-c)	CTUh	2.09E-07	1.10E-12	2.89E-09	8.82E-10	2.77E-08	2.41E-07	-2.28E-09
Human toxicity, non-cancer (PEF-CTUh-nc)	CTUh	1.51E-07	2.46E-11	8.67E-11	1.18E-08	1.59E-08	1.79E-07	-1.81E-07
Ionising radiation, human health (PEF-IR)	kg Bq U235 eq.	2.97E+01	1.53E-04	4.66E-03	1.10E+01	5.78E-03	4.07E+01	-4.10E-03
Land use (PEF-LU)	No dimension	2.73E-01	0.00E+00	6.99E-05	3.64E-01	3.45E-01	9.82E-01	-2.30E+00
Ozone depletion (PEF-ODP)	kg CFC-11 eq.	2.40E-07	9.65E-11	3.47E-10	3.82E-08	1.13E-08	2.90E-07	-8.86E-09
Photochemical ozone formation - human health (PEF-POCP)	kg of NMVOC eq.	7.91E-03	1.72E-03	5.28E-05	1.15E-02	5.02E-04	2.17E-02	-2.70E-03
Resource use, fossils (PEF-ADPf)	MJ	4.49E+01	9.39E-01	2.64E-01	1.81E+02	1.35E+00	2.29E+02	-1.73E+00
Resource use, minerals and metals (PEF-ADPe)	kg Sb eq	2.84E-04	2.65E-09	6.75E-10	2.70E-06	-5.10E-07	2.86E-04	-4.88E-05
Water use (PEF-WU)	m3 eq.	2.44E+00	2.44E-04	2.35E-03	4.83E-01	2.93E+01	3.22E+01	-1.37E+02

Resource use indicators

Indicators	Unit	Manufacturing A1-A3	Distribution A4	Installation A5	Use B1-B7	End Of Life C1-C4	GLOBAL	Module D
Net use of fresh water	m³	5.68E-02	5.68E-06	5.47E-05	1.16E-02	8.01E-01	8.69E-01	-3.22E+00
Total use of primary energy	MJ	4.66E+01	9.40E-01	3.00E-01	2.59E+02	1.48E+00	3.09E+02	-2.19E+00
Total use of non renewable primary energy resources	MJ	4.49E+01	9.39E-01	2.64E-01	1.81E+02	1.35E+00	2.29E+02	-1.73E+00
Total use of renewable primary energy resources	MJ	1.72E+00	1.20E-03	3.57E-02	7.81E+01	1.38E-01	8.00E+01	-4.65E-01
Use of non-renewable primary energy, excluding non renewable primary energy resources used as raw materials	MJ	4.05E+01	9.39E-01	2.64E-01	1.81E+02	1.35E+00	2.24E+02	-1.73E+00
Use of non-renewable primary energy resources as raw materials	MJ	4.31E+00	0.00E+00	0.00E+00	0.00E+00	0.00E+00	4.31E+00	0.00E+00
Use of non-renewable secondary fuels	MJ	0.00E+00	0.00E+00	0.00E+00	0.00E+00	0.00E+00	0.00E+00	0.00E+00
Use of renewable primary energy, excluding renewable primary energy resources used as raw materials	kg	1.09E+00	1.20E-03	3.57E-02	7.81E+01	1.38E-01	7.94E+01	-4.65E-01
Use of renewable primary energy resources as raw materials	MJ	6.32E-01	0.00E+00	0.00E+00	0.00E+00	0.00E+00	6.32E-01	0.00E+00
Use of renewable secondary fuels	MJ	0.00E+00	0.00E+00	0.00E+00	0.00E+00	0.00E+00	0.00E+00	0.00E+00
Use of secondary materials	kg	3.62E-06	0.00E+00	0.00E+00	0.00E+00	0.00E+00	3.62E-06	0.00E+00

Waste category indicators

Indicators	Unit	Manufacturing A1-A3	Distribution A4	Installation A5	Use B1-B7	End Of Life C1-C4	GLOBAL	Module D
Hazardous waste disposed	kg	6.72E+00	0.00E+00	6.49E-04	6.30E-01	2.90E-02	7.38E+00	0.00E+00
Non-hazardous waste disposed	kg	4.25E-01	2.26E-03	1.31E-02	9.13E-01	7.91E-02	1.43E+00	0.00E+00
Radioactive waste disposed	kg	1.98E-04	1.57E-06	1.45E-06	4.11E-04	1.95E-06	6.14E-04	0.00E+00

Output flow indicators

Indicators	Unit	Manufacturing A1-A3	Distribution A4	Installation A5	Use B1-B7	End Of Life C1-C4	GLOBAL	Module D
Components for re-use	kg	0.00E+00	0.00E+00	0.00E+00	0.00E+00	0.00E+00	0.00E+00	0.00E+00
Exported energy	MJ	0.00E+00	0.00E+00	0.00E+00	0.00E+00	0.00E+00	0.00E+00	0.00E+00
Materials for energy recovery	kg	0.00E+00	0.00E+00	3.32E-03	0.00E+00	0.00E+00	3.32E-03	0.00E+00
Materials for recycling	kg	2.33E-02	0.00E+00	1.29E-03	0.00E+00	0.00E+00	2.46E-02	0.00E+00

Biogenic carbon content

Packaging	Unit	Cardboard	Paper	Wood	Sum
Biogenic carbon content (ratio)	%	2.80E+01	3.78E+01	3.95E+01	
Mass	kg	2.77E-02	1.52E-03	6.15E-03	3.54E-02
Biogenic carbon content (declared unit)	kg of C	7.76E-03	5.74E-04	2.43E-03	1.08E-02
Biogenic carbon content (functional unit)	kg of C	7.76E-03	5.74E-04	2.43E-03	1.08E-02
Source		ADEME	APESA/RECORD	EN 16485	


Product	Unit	Cardboard	Paper	Wood	Sum
Mass	kg	0.00E+00	0.00E+00	0.00E+00	0.00E+00
Biogenic carbon content (declared unit)	kg of C	0.00E+00	0.00E+00	0.00E+00	0.00E+00
Biogenic carbon content (functional unit)	kg of C	0.00E+00	0.00E+00	0.00E+00	0.00E+00

Extrapolation rules

For the references covered by this PEP, the extrapolation factor had been calculated according to the weight ratio, please see the following table :

INTERNAL REF	COMMERCIAL REF	DESCRIPTION	MANUFACTURING	DISTRIBUTION	INSTALLATION	USE	EOL
WMSS82-USBCC	WMSS82-USBCC	13A 2G DP Sw.Socket USB C+C PD	1.00	1.00	1.00	1.00	1.00
WMSS82G-USBCC	WMSS82G-USBCC	13A 2G DP Sw.Socket USB C+C PD Grey	1.07	1.00	1.00	1.00	1.00
WRSS82BSB-USBCC	WRSS82BSB-USBCC	13A 2G DP Sw.Socket USB C+C BSB Raised	1.23	1.25	1.18	1.00	1.29
WRSS82BSW-USBCC	WRSS82BSW-USBCC	13A 2G DP Sw.Socket USB C+C BSW Raised	1.23	1.24	1.18	1.00	1.27
WRSS82PSB-USBCC	WRSS82PSB-USBCC	13A 2G DP Sw.Socket USB C+C PSB Raised	1.23	1.24	1.18	1.00	1.29
WRSS82PSW-USBCC	WRSS82PSW-USBCC	13A 2G DP Sw.Socket USB C+C PSW Raised	1.23	1.24	1.18	1.00	1.27
WFSS82BSB-USBCC	WFSS82BSB-USBCC	13A 2G DP Sw.Socket USB C+C PD BSB Flat	2.24	1.47	1.18	1.00	1.45
WFSS82BSW-USBCC	WFSS82BSW-USBCC	13A 2G DP Sw.Socket USB C+C PD BSW Flat	2.19	1.47	1.18	1.00	1.44
WFSS82PSB-USBCC	WFSS82PSB-USBCC	13A 2G DP Sw.Socket USB C+C PD PSB Flat	2.24	1.48	1.18	1.00	1.45
WFSS82PSW-USBCC	WFSS82PSW-USBCC	13A 2G DP Sw.Socket USB C+C PD PSW Flat	2.19	1.47	1.18	1.00	1.44
WPSS82-USBCC	WPSS82-USBCC	13A 2G DP Sw.Socket USB C+C Metal Grey	1.32	1.31	1.36	1.00	1.29
WPSS82B-USBCC	WPSS82B-USBCC	13A 2G DP Sw.Socket USB C+C Mtl Bx w/oKO	2.11	2.28	1.60	1.00	1.91
WPSS82BKO-USBCC	WPSS82BKO-USBCC	13A 2G DP Sw.Sockt USB C+C Mtlcd Bx w/KO	2.11	2.27	1.60	1.00	1.91
WPSS82W-USBCC	WPSS82W-USBCC	13A 2G DP Sw.Sockt USB C+C Metal White	1.32	1.31	1.36	1.00	1.29

Verification

Registration N°: HAGE-00839-V01.01-EN	Drafting Rules	PEP-PCR-ed4-2021 09 06
	Supplemented by	PSR-0005-ed3-2023 06 06
Verifier accreditation N°: VH37	Information and reference documents: www.pep-ecopassport.org	
Date of issue: 8-2024	Validity period:	5 years
Independent verification of the declaration and data, in compliance with ISO 14025 : 2006		
Internal ● External ○		
The PCR review was conducted by a panel of experts chaired by Julie Orgelet (DDemain)		
PEPs are compliant with XP C08-100-1:2016 or EN 50693:2019		
The elements of the present PEP cannot be compared with elements from another program.		
Document in compliance with ISO 14025 : 2006 « Environmental labels and declarations. Type III environmental declarations »		

Nota :

The picture has no contractual value.

All numerical values indicated in this document may vary and depend of many factors such as the tolerance related to materials, the usage and environment conditions of the products, installation characteristics ... , real values for a product in a concrete application may therefore change.

The usage time mentioned in this document is an average duration chosen for the need of the calculations. This value cannot be assimilated to the minimum, average or real life time.

The responsibility of the company, issuing this document, can never be engaged if differences would be noticed between the values given by this document and real ones, whatever the causes and/or consequences would be.