

# Adhesive smoke seal (4.5m)

**Catalogue numbers:**  
JPASMSEAL2

## Specifications:

### Regulatory

- REACH and RoHS certified

### Product Description

- 3.2mm thick closed cell EPDM foam tap with an adhesive on one side
- EPDM foam is non-staining, non-corrosive and electrically non-conductive
- EPDM foam is also non-toxic and flame retardant
- EPDM foam offers high temperature resistance(-40 C to 115 C) as well as resistance to UV light and ozone

### Application Fields

- Ideal sealing solution for enclosure/switchboard
- Ideal sealing solution for electrical enclosure/switch cabinets

### Materials

- Backing - EPDM rubber foam
- Type of adhesive - acrylic

### Properties / Performance Values

|                                  |           |
|----------------------------------|-----------|
| Tensile strength                 | 16N/cm    |
| Hardness - Shore 00              | 34 STK    |
| Temperature resistance min.      | -40°C     |
| Temperature resistance max.      | 115°C     |
| Thermal conductivity z-direction | 0.05 W/mK |
| Water resistance                 | Very good |

### Adhesion to values

|       |         |
|-------|---------|
| Steel | 5.5N/cm |
|-------|---------|

