


- DE Montageanleitung
- FR Notice d'instructions
- GB Mounting instructions
- IT Istruzioni di montaggio

uniway UW-Sxxx


- DE Stecksockel 125A, 160A, 250A
- FR Socle enfichable 125A, 160A, 250A
- EN Busbar socket 125A, 160A, 250A
- IT Zoccolo a innesto 125A, 160A, 250A



UW-Sxxx




	U_e max.	I_n max.	I_{cw} max.
UW-S125-xx	690 V AC	125 A	10 kA / 300 ms
UW-S160-xx	690 V AC	160 A	10 kA / 300 ms
UW-S250-xx	690 V AC	250 A	12 kA / 300 ms



UW-SE



UW-PE



EN 60715

UW-K52	5x2mm	2m
UW-K103	10x3mm	2m
UW-K153	15x3mm	2m
UW-K253	25x3mm	2m




UW-Kx
Cu-ETP CW004A
(EN 13601)







M6	L
UW-S125-xx	50mm
UW-S160/250A-xx	65mm




SW6 (M = 4 Nm)







UW-SE




1




2 UW-S125-xx








UW-S160-xx/250-xx




3









UW-PE



U_e max.	400 V AC
I_n max.	63 A





Hauptsitz

Hager AG
Sedelstrasse 2
CH-6020 Emmenbrücke

Tel. +41 41 269 90 00

Verkaufsniederlassungen

Hager AG
Glattalstrasse 521
CH-8153 Rümlang

Tel. +41 44 817 71 71

Hager AG
Ey 25
CH-3063 Ittigen-Bern

Tel. +41 31 925 30 00

Hager AG
Chemin du Petit-Flon 31
CH-1052 Le Mont-sur-Lausanne

Tel. +41 21 644 37 00

hager.ch
infoch@hager.com