



## Hager Muse Mounting box

Cat. no:  
**WGMB351**  
**WGMB352**



### 1. USE


Device to provide surface-mounting for wiring accessories  
Completed delivery supply without two 25mm fixing screws

### 2. RANGE

Hager Muse: White

Description	White	Aurora Silver	Knight Black
1 gang mounting box	WGMB351	NA	NA
2 gang mounting box	WGMB352	NA	NA

### 3. DIMENSIONS



Reference	A	B	C	
WGMB351	146mm	86mm	37.8mm	
WGMB352	86mm	86mm	37.8mm	

### 4. TECHNICAL CHARACTERISTICS

#### 4.1 Application

Surface mounting;  
Suit for full range of hager Muse, except key tag switch;

#### 4.2 Material for key components

PC: White Polycarbonate with UV resistance (PC) RAL9010  
Terminal: Brass

#### 4.3 Material characteristic

Colour: White: PC  
Self-extinguishing: 650°C / 30s

#### 4.4 Climatic characteristics

Storage temperature: -20°C to +70°C  
Operating temperature: -20°C to +35°C

### 5. STANDARDS AND APPROVALS

Certifications: Accredited lab test report  
Standards: IEC 60670-1;

### 6. MAINTENANCE

Surface cleaning with a cloth.  
Do not use: acetone, tar remover, trichlorethylene.  
Maintenance with the following products: Hexane(EN 60669-1),  
Methylated spirit, Soapy water, Diluted ammonia, Bleach diluted  
to 10%, window - cleaning products.

Caution: A preliminary test should be carried out if other specific  
cleaning products are to be used.

### 7. CONNECTIONS

Distance of installation hole: 60.3mm for 1gang mounting box,  
120.6mm for 2 gang mouning box;

Maximum mounting screw torque: 0.6 N.m

