


Hager Muse Single pole switched BS socket

Cat. no: WGMS115S




1. USE

Device to provide power for electrical equipments
Completed delivery supply with two 37mm fixing screws for
flush-mounting or surface-mounting boxes

2. RANGE

15A 1G Single pole switched socket		
White	Aurora Silver	Knight black
WGMS115S	WGMS115SAS	WGMS115SKB

3. DIMENSIONS



Description	A	B	C	D
WGMS115S**	86±0.3mm	86±0.3mm	23mm	34mm

4. TECHNICAL CHARACTERISTICS

4.1 Rating

Current: 15A

Voltage: 250V~, 50/60Hz

4.2 Material for key components

Frame: White Polycarbonate with UV resistance (PC) RAL9010

Front plate: White Polycarbonate with UV resistance (PC) RAL9010

Base: Nylon, Color Pantone: 429U

Moving Contact: Brass Strip, Onlay

Silver Revit: AgNi10

4.3 Material characteristic

White: PC

Color: Lacquering on the white PC

Self-extinguishing: 650°C / 30s

4.4 Climatic characteristics

Storage temperature: -20°C to +70°C

Operating temperature: -20°C to +35°C

5. STANDARDS AND APPROVALS

Certifications: Accredited lab certificate/ test report

Standards: BS 546; SS 472; MS 1577

6. MAINTENANCE

Surface cleaning with a cloth.

Do not use: acetone, tar remover, trichlorethylene.

Maintenance with the following products: Hexane(EN 60669-1), Methylated spirit, Soapy water, Diluted ammonia, Bleach diluted to 10%, window - cleaning products.

Caution: A preliminary test should be carried out if other specific cleaning products are to be used.

7. CONNECTIONS

Distance of installation hole: 60.3mm

Terminal capacity: 3 x 2.5mm² or 2 x 4.0mm²

Cable Strip length: 12mm

Maximum mounting screw torque: 0.6 N.m

Contact terminal screw torque: 1.2N.m

