



## Hager Dream 25A DP 1 gang 1 way switch

Cat. no: WGDL25D1N



### 1. USE


Device to switch on/off the load  
Completed delivery supply with two 37mm fixing screws  
for flush-mounting or surface-mounting boxes

### 2. RANGE

#### 25A DP 1 gang 1 way switches with LED

White	Interstellar Grey	Noble Bronze	Knight black	Elegant Gold
WGDL25D1N	NA	NA	NA	NA

### 3. DIMENSIONS



Description	A	B	C	D
WGDL25D1N	86mm	86mm	13mm	29.2mm

### 4. TECHNICAL CHARACTERISTICS

#### 4.1 Rating

Current: 25A

Voltage: 250V~, 50/60Hz

#### 4.2 Material for key components

Frame: White Polycarbonate with UV resistance (PC) RAL9010

Front plate: White Polycarbonate with UV resistance (PC) RAL9010

Base: Nylon, Color Pantone: 429U

Moving Contact: Brass Strip, Onlay

Silver Revit: AgNi10

#### 4.3 Material characteristic

White: PC

Color: Lacquering on white PC

Self-extinguishing: 650°C / 30s

#### 4.4 Climatic characteristics

Storage temperature: -20°C to +70°C

Operating temperature: -5°C to +45°C

### 5. STANDARDS AND APPROVALS

Certifications: Accredited lab certificate/ test report

Standards: IEC 60669-1

### 6. MAINTENANCE

Surface cleaning with a cloth.

Do not use: acetone, tar remover, trichlorethylene.

Maintenance with the following products: Hexane(EN 60669-1), Methylated spirit, Soapy water, Diluted ammonia, Bleach diluted to 10%, window - cleaning products.

Caution: A preliminary test should be carried out if other specific cleaning products are to be used.

### 7. CONNECTIONS

Distance of installation hole: 60.3mm

Terminal capacity: 2 x 4.0mm<sup>2</sup>

Cable Strip length: 12mm

Maximum mounting screw torque: 0.6 N.m

Contact terminal screw torque: 1.2N.m

