



AE982B

**RCBO 1P+N 6kA C-32A 100mA AC Class**

**Technical Features**

**Architecture**

Type of pole	1P+N
Curve	C

**Electric current**

Rated current	32 A
Rated residual operating current I <sub>dn</sub>	100 mA
Rated current -25°C	38.30 A
Rated current at -20°C	37.80 A
Rated current -15°C	37.20 A
Rated current -10°C	36.70 A
Rated current -5°C	36.10 A
Rated current at 0°C	35.60 A
Rated current 5°C	35 A
Rated current 10°C	34.40 A
Rated current 15°C	33.80 A
Rated current at 20°C	33.20 A
Rated current 25°C	32.60 A
Rated current 30°C	32 A
Rated current 35°C	31.50 A
Rated current at 40°C	31 A
Rated current at 45°C	30.50 A
Rated current at 50°C	30 A
Rated current 55°C	29.50 A
Rated current 60°C	29 A
Correction factor of rating current for 2 devices placed side by side	1
Min./max. threshold value of the AC thermal operation	1.13 - 1.45 A
Correction factor of rating current for 3 devices placed side by side	0.95
Correction factor of rating current for 4 and 5 devices placed side by side	0.90
Correction factor of rating current for 6 devices placed side by side	0.85

**Safety**

Residual current type	AC
Ingress Protection (IP) class	IP20

**Main electrical attributes**

Rated short-circuit breaking capacity I <sub>cn</sub> AC according to IEC 60898-1	6 kA
---	------

**Connectivity**

Type of connection	Screw terminal
--------------------	----------------

**Voltage**

Rated insulation voltage U <sub>i</sub>	500 V
---	-------

**Electric current**

Rated service breaking capacity I <sub>cs</sub> AC according to IEC 60898-1	6 kA
---	------

**Voltage**

Rated impulse withstand voltage U <sub>imp</sub>	4000 V
Max. operating voltage	240 V
Rated operational voltage U <sub>e</sub>	240 - 240 V
Overvoltage category according to IEC 60947-1	3

**Power**

Total power loss under I <sub>N</sub>	7.60 W
---------------------------------------	--------

**Frequency**

Frequency	50 - 50 Hz
-----------	------------

---

**Use conditions**

---

Max. Altitude	2000 m
---------------	--------

---

**Installation, mounting**

---

Nominal tightening torque down terminal	2.10 - 2.10 Nm
Nominal tightening torque top terminal	2.10 - 2.10 Nm

---

**Use conditions**

---

Class of energy limitation I <sup>2</sup> t	3
---	---

---

**Endurance**

---

Electric endurance in number of cycles	2000
Number of mechanical operations	1000

---

**Connection**

---

Cross-section rigid conductor	1 - 25 mm <sup>2</sup>
-------------------------------	------------------------

---

**Installation, mounting**

---

Nominal tightening torque	2.10 - 2.10 Nm
---------------------------	----------------

---

**Capacity**

---

Number of modules	2
-------------------	---

---

**Dimensions**

---

Height	83 mm
Width	35 mm
Depth	68 mm

---

**Use conditions**

---

Operating temperature	-25 - 40 °C
Storage/transport temperature	-25 - 70 °C
Degree of pollution according to IEC 60664 / IEC 60947-2	2
Air humidity protection	For all climates

---