



FW324WT

Surface encl. FW2, IP30, class I, with door and brass terminals, 3x24 modules

### Technical Features

#### Installation, mounting

Suitable for outdoor usage	No
Mounting on	Surface mounting

#### Electric current

Rated current	125 A
---------------	-------

#### Equipment

Number of rows	3
Number of section in width	2
With lock	No
Has neutral terminal block	No

#### Capacity

Number of modules	72
-------------------	----

#### Dimensions

Height	641 mm
Width	571 mm
Depth	150 mm

#### Cover, door

Number of cabinet doors	1
-------------------------	---

#### Dimensions

Number of width units	24
-----------------------	----

#### Cover, door

Door/cover is transparent	No
---------------------------	----

#### Connection

Number of conduit inlets	2
--------------------------	---

#### Materials

Material	Steel
RAL code	9010
Colour	Pure white

#### Equipment

Has earthing terminal block	Yes
Has mounting plate	No

#### Safety

Protection class	Isolation class I
Impact resistance IK	IK08
Ingress Protection (IP) class	IP30
Locking type	Key lock Without lock