

Consumer Unit Design Evo Switch Disconnecter Incomer

For the distribution of power in a residential application, conforming to BS EN 61439-3 including Annex ZB (16kA rating).



VME106

Design Evo is the enhanced board for use in applications where the consumer unit is located in a living area of the dwelling.

The single row range of consumer units with a 116A rated current (InA) have been designed for installations where the upstream overcurrent protection device (OCPD) is rated at 100A or below, the 116A (InA) is where the consumer unit can be used with a 16A generation set when the bi-directional RCBO can be installed at the far end of the busbar.

(This is not applicable in Dual Row enclosures)

Description	Size	Cat ref.
2 Way 63A Switch Disconnecter Incomer - 63A InA	3	VME202
6 Way 100A Switch Disconnecter Incomer - 116A InA	3	VME106
10 Way 100A Switch Disconnecter Incomer - 116A InA	4	VME110
14 Way 100A Switch Disconnecter Incomer - 116A InA	5	VME114
20 Way 100A Switch Disconnecter Incomer - 116A InA	7	VME120

Features & Benefits

- Cable clamp - Secures supply cables on entry to main incoming device preventing any movement being transmitted through meter tails to device
- Round cable entry points top, bottom and sides
- Rear Knockouts for ease of cable entry - Cable protector plate provided
- Rigid top wall - Enhances rigidity to prevent distortion when removing knockouts
- Locate and hold cover - allows use of both hands whilst fixing cover
- Front cover retained screws - Prevents loss during installation
- Full metal DIN rail - Secure and stable attachment of devices
- Quick release clip on MCB/RCBO - Allows removal of MCB/RCBO with busbar still in place
- Optimised cabling space - DIN rail position allows maximum cabling space
- Top mounted terminal rail makes the wiring of the neutral and earth connections neat and simple.
- Torque settings displayed inside front cover so they're easily accessible by the electrician.
- Single row references have a 116A InA.

Technical Characteristics

Standards	BS EN 61439-3
Classification	Consumer Unit
Rated & Operational Voltage (U_n/U_e)	230V a.c 50 Hz
Rated Insulation Voltage (U_i)	320V a.c. 50Hz
Rated Frequency (fn)	50 Hz
Rated impulse withstand voltage (U_{imp})	4kV
Rated Current of the Assembly (I_n)	116A
Rated Current of an Outgoing Circuit I_{nC}	RCBO ADB4**G - 40A - 50A (Marked Rated Current on Device) RCBO ADB9**R - 6A - 32A (Marked Rated Current on Device)
Rated Conditional Short Circuit of the Assembly (I_{cc})	Annex ZB: 16kA rms at 250V, power factor 0.6 with equipment and arrangements specified in Hager's technical documentation/catalogue
Protection against electric shock	Consumer Unit shall be installed in an electrical system conforming to IEC 60364 / BS 7671
Rated Diversity Factor (RDF) / Values of assumed loading	2 Way to 3 Way - 0.8, 4 Way to 5 Way - 0.7, 6 Way to 9 Way - 0.6, 10 Way and above - 0.5
<p>Note: RDF only applies to continuously and simultaneously loaded circuits. In principle, this means adjacent circuit breakers having a load on time exceeding 30 minutes or where a load not exceeding 30 minutes has an 'off' time less than the 'on' time will need to have the rated diversity factor applied as indicated.</p>	
Pollution Degree	2
Types of System Earthing for which the assembly is designed	TT, TNC-S and TN-S when installed in an electrical system conforming to BS 7671
Intended locations	Indoor use only
Stationary assembly	
Degree of protection	IP2XC with door open / closed and full compliment of devices / blanks fitted. Note: Where cables are installed through the top wall of the enclosure, gaps of IP4X to be maintained.
Intended use	Intended for use in domestic (residential) or similar premises
Electromagnetic compatibility (EMC) classification	EMC environment B
External design	Wall mounted, surface type, enclosed assembly.
Mechanical impact protection	IK05
Type of construction	Fixed parts
Incoming Line/Neutral terminal (80 - 100A board)	50mm ²
Incoming Line/Neutral terminal (63A board)	25mm ²
Incoming Earth Terminal	16mm ²
Warranty - Hager undertakes to replace or repair at its discretion products should they become inoperable within the time periods as stated. - 2 Years	

Accessories

Cable protector plate	Provides protection for cables entering from the rear of the board	VM02CE
Rear stand off plates	To stand consumer unit off wall allowing surface mounted cables to enter through rear of unit.	VM01SP

Devices

Single Pole, Single Mod RCBO 6kA, 40A - 50A Type A	ADB4**G
Bidirectional RCBO 1M 1P+N 6kA B Curve 6A 30mA A	ADB9**R

Design Dimensions (mm)

	Enclosure Size				
	2	3	4	5	7
Height	240	240	240	240	240
Width	149	221	293	364	472
Depth	102.5	102.5	102.5	102.5	102.5

