





6LE090970D



quickguide






- DE flow R3 Hybrid Wechselrichter
- EN flow R3 Hybrid inverter
- NL flow R3 Hybride omvormer














flow R3
XEM1200 - XEM4x0x



More Information:
[hgr.io/d/XEM1200/](https://hgr.io/d/XEM1200/ProductInstallationManual)
ProductInstallationManual

flow R3
<https://hager.click/htv>





i

Ethernet - / LAN

OPT1	
1	24V+
2	24VGND
3	EXT NAIN1
4	EXT NAIN2
5	EXT NAO UT1
6	EXT NAO UT2
7	EXT EMIN
8	EXT EMOUT
9	NOA
10	COMA
11	NOB
12	COMB

OPT2	
1	24VGND
2	24VGND
3	CANH
4	CANH
5	CANL
6	CANL
7	24V+
8	24V+

OPT3	
1	INA1
2	INA2
3	INB1
4	INB2

SYN1	
1	CAN-Syn-H
2	CAN-Syn-L
3	CAN-Syn-GND
4	Syn-H
5	Syn-L

SYN2	
1	CAN-Syn-H
2	CAN-Syn-L
3	CAN-Syn-GND
4	Syn-H
5	Syn-L

ATS	
1	CG
2	AL
3	AH
4	CG
5	G
6	ML
7	MH
8	24V

