

EU Declaration of Conformity No. 26.3014.04.26

We Hager Electro GmbH & Co. KG
Zum Gunterstal
66440 BLIESKASTEL - GERMANY

**declare that the product(s)
designation**

Hager Consumer Unit Range
Type: Surface

type reference(s)

Design 10: VML
Design 30: VM

trademark

Hager

is (are) in conformity with the relevant Union harmonization legislation:

- Directive on the Restriction of the use of certain Hazardous Substances (RoHS) No. 2011/65/EU amended by No. 2015/863/EU
- Electromagnetic Compatibility Directive (EMCD) No. 2014/30/EU
- Low Voltage Directive (LVD) No. 2014/35/EU
- Packaging and Packaging Waste Regulation (PPWR) No. 2025/40/EU

.....

.....

Standard number + relevant amendments together with the edition dates and/or relevant document(s)

BS EN 61439-3: 2012 incorporating corrigenda September 2013 and December 2015 and March 2019

EN IEC 63000:2018

If applicable, mention here for radio products, the data about notified body. See RED directive - Annex VI - point 7

We additionally confirm compliance with the EU Directives & Regulations, which are not linked to CE marking (if applicable).
See document DMS103207 'General EU Declaration of Conformity'.

This declaration of conformity is issued under the sole responsibility of the manufacturer.

On behalf of Hager Electro GmbH & Co. KG - Zum Gunterstal - 66440 BLIESKASTEL - GERMANY

Name of signatory

Ian ELLIS

Function of signatory

Certification Mandatee

Place and date of issue

Telford UK, 15th June 2026

Signature

Ian Ellis

EU DECLARATION OF CONFORMITY

No. 26.3014.04.26

Type References:

Consumer Unit Design 10 Range

Design 10	No. Of Outgoing Circuits	Product Description
VML402AH	2	2 Way 63A 30mA Type A RCCB Incomer
VML406AH	6	6 Way 63A 30mA Type A RCCB Incomer
VML306AH	6	6 Way 100A 30mA Type A RCCB Incomer
VML410AH	10	10 Way 63A 30mA Type A RCCB Incomer
VML310AH	10	10 Way 100A 30mA Type A RCCB Incomer
VML314AH	14	14 Way 100A 30mA Type A RCCB Incomer
VML633H	6	6 Way Split load 3+3 63A Switch 2*63A Type A RCCB
VML655H	10	10 Way Split load 5+5 63A Switch 2*63A Type A RCCB
VML666H	12	12 Way Split load 6+6 63A Switch 2*63A Type A RCCB
VML610CU	10	12 Way High Integrity Split Load Configurable 63A Switch 2*63A 30mA Type A RCCB
VML612CU	12	12 Way High Integrity Split Load Configurable 63A Switch 2*63A 30mA Type A RCCB
VML616CU	16	12 Way High Integrity Split Load Configurable 63A Switch 2*63A 30mA Type A RCCB
VML24AH	2	2 Way 40A 30mA RCCB with 1*32A & 1*6A MCB
VML512AC	12	12 Way Configurable, 100A Switch 1x 100A 30mA RCCB (Remaining Ways for RCBOs)
VML518AC	18	18 Way Configurable, 100A Switch 1x 100A 30mA RCCB (Remaining Ways for RCBOs)

Design 10 with Knockouts	No. Of Outgoing Circuits	Product Description
VML402AHK	2	2 Way 63A 30mA Type A RCCB Incomer
VML406AHK	6	6 Way 63A 30mA Type A RCCB Incomer
VML306AHK	6	6 Way 100A 30mA Type A RCCB Incomer
VML410AHK	10	10 Way 63A 30mA Type A RCCB Incomer
VML310AHK	10	10 Way 100A 30mA Type A RCCB Incomer
VML314AHK	14	14 Way 100A 30mA Type A RCCB Incomer
VML633HK	6	6 Way Split load 3+3 63A Switch 2*63A Type A RCCB
VML655HK	10	10 Way Split load 5+5 63A Switch 2*63A Type A RCCB
VML666HK	12	12 Way Split load 6+6 63A Switch 2*63A Type A RCCB
VML610CUK	10	12 Way High Integrity Split Load Configurable 63A Switch 2*63A 30mA Type A RCCB
VML612CUK	12	12 Way High Integrity Split Load Configurable 63A Switch 2*63A 30mA Type A RCCB
VML616CUK	16	12 Way High Integrity Split Load Configurable 63A Switch 2*63A 30mA Type A RCCB
VML24AHK	2	2 Way 40A 30mA RCCB with 1*32A & 1*6A MCB
VML512ACK	12	12 Way Configurable, 100A Switch 1x 100A 30mA RCCB (Remaining Ways for RCBOs)
VML518ACK	18	18 Way Configurable, 100A Switch 1x 100A 30mA RCCB (Remaining Ways for RCBOs)

EU DECLARATION OF CONFORMITY

No. 26.3014.04.26

Type References:

Consumer Unit Design 30 Range

Design 30	No. Of Outgoing Circuits	Product Description
VM402AH	2	2 Way 63A 30mA Type A RCCB Incomer
VM406AH	6	6 Way 63A 30mA Type A RCCB Incomer
VM306AH	6	6 Way 100A 30mA Type A RCCB Incomer
VM410AH	10	10 Way 63A 30mA Type A RCCB Incomer
VM310AH	10	10 Way 100A 30mA Type A RCCB Incomer
VM314AH	14	14 Way 100A 30mA Type A RCCB Incomer
VM633H	6	6 Way Split load 3+3 63A Switch 2*63A Type A RCCB
VM655H	10	10 Way Split load 5+5 63A Switch 2*63A Type A RCCB
VM666H	12	12 Way Split load 6+6 63A Switch 2*63A Type A RCCB
VM610CU	10	12 Way High Integrity Split Load Configurable 63A Switch 2*63A 30mA Type A RCCB
VM612CU	12	12 Way High Integrity Split Load Configurable 63A Switch 2*63A 30mA Type A RCCB
VM616CU	16	12 Way High Integrity Split Load Configurable 63A Switch 2*63A 30mA Type A RCCB
VM24AH	2	2 Way 40A 30mA RCCB with 1*32A & 1*6A MCB
VM512AC	12	12 Way Configurable, 100A Switch 1x 100A 30mA RCCB (Remaining Ways for RCBs)
VM512AC	12	12 Way Configurable, 100A Switch 1x 100A 30mA RCCB (Remaining Ways for RCBs)
VM518AC	18	18 Way Configurable, 100A Switch 1x 100A 30mA RCCB (Remaining Ways for RCBs)
VM518AC	18	18 Way Configurable, 100A Switch 1x 100A 30mA RCCB (Remaining Ways for RCBs)

Design 30	No. Of Outgoing Circuits	Product Description
VM402AHK	2	2 Way 63A 30mA Type A RCCB Incomer
VM406AHK	6	6 Way 63A 30mA Type A RCCB Incomer
VM306AHK	6	6 Way 100A 30mA Type A RCCB Incomer
VM410AHK	10	10 Way 63A 30mA Type A RCCB Incomer
VM310AHK	10	10 Way 100A 30mA Type A RCCB Incomer
VM314AHK	14	14 Way 100A 30mA Type A RCCB Incomer
VM633HK	6	6 Way Split load 3+3 63A Switch 2*63A Type A RCCB
VM655HK	10	10 Way Split load 5+5 63A Switch 2*63A Type A RCCB
VM666HK	12	12 Way Split load 6+6 63A Switch 2*63A Type A RCCB
VM610CUK	10	12 Way High Integrity Split Load Configurable 63A Switch 2*63A 30mA Type A RCCB
VM612CUK	12	12 Way High Integrity Split Load Configurable 63A Switch 2*63A 30mA Type A RCCB
VM616CUK	16	12 Way High Integrity Split Load Configurable 63A Switch 2*63A 30mA Type A RCCB
VM24AHK	2	2 Way 40A 30mA RCCB with 1*32A & 1*6A MCB
VM512AC	12	12 Way Configurable, 100A Switch 1x 100A 30mA RCCB (Remaining Ways for RCBs)
VM512ACK	12	12 Way Configurable, 100A Switch 1x 100A 30mA RCCB (Remaining Ways for RCBs)
VM518AC	18	18 Way Configurable, 100A Switch 1x 100A 30mA RCCB (Remaining Ways for RCBs)
VM518ACK	18	18 Way Configurable, 100A Switch 1x 100A 30mA RCCB (Remaining Ways for RCBs)

Consumer Unit Accessories – Design 10/30

CU Accessories	Product Description
JK01B	Single Pole Blank
VM01CE	Cble Protector Plate (Metal)
VM02CE	Cable Protector Plate (Plastic)
VA10MT	Cable Clamp for Metal Tails

EU DECLARATION OF CONFORMITY

NO. 26.3014.04.26

Evidence(s)

Documents listed below have been used in order to establish the conformity to the essential requirements of the relevant directives:

Conformity report / evidence:	Hager UK Test report G1931-1a Design 10 & Design 30 range CDB Hager UK Test Report G2133 BS EN 61439-3 Corrigenda March 2019 Hager Group Short circuit Test report N° HOM 14371 Hager Group Short circuit Test report N° HOM 14372 Hager Group Short circuit Test report N° HOM 15201 Hager Group salt mist test report 18-088LAB-BLK Hager Group RoHS risk analysis DMS045428 Hager Group EU DoC N° 19.1516.06.19 16A – 125A Switch Disconnected Hager Group EU DoC No 19.1690.06.19 63A Type A RCCB Hager Group EU DoC N° 18.1441.11.18 6kA RCBO Hager Group EU DoC N° 19.1715.01.19 6kA MTN MCB Routine Test program for VM & VML Non-combustible CU
Product documentation:	See Hager website
Comments:	None

Signature (technical design)

Name of signatory

Thierry LIENHARDT

Function of signatory

Engineering Director

Place and date of issue

Obernai FR, 15th June 2026

Signature

