













vega

VB118 + VB218: 90A / 400V

VB318 + VB418: 125A / 400V



hager.com











PZ2


 $\varnothing$ 8 mm


	H [mm]	W [mm]	D [mm]	D ₂ [mm]
VB118	325	400	146	126
VB218	475	400	146	126
VB318	625	400	146	126
VB418	775	400	146	126

01





10









✓ Cu







⚠

✗

			Class 1*	Class 2*	Class 5*
C1	2x M4	1,7Nm	10 - 16 mm ²	10 - 25 mm ²	
C2	M5	2,3Nm	1,5 - 16 mm ²	1,5 - 10 mm ²	
C3	M4	1,7Nm	1,5 - 10 mm ²		

* IEC 60228





Reference	Admissible thermal dissipation loss for wall mounted distribution boards at temperature rise ΔT [1]					
	10K W	15K W	20K W	25K W	30K W	Enclosure height [%]
VB118x	9,2	15,3	21,8	28,8	36,1	100
	11,0	18,2	26,1	34,4	43,1	50
VB218x	11,5	19,0	27,2	35,9	45,0	100
	14,5	24,1	34,4	45,4	57,0	50
VB318x	13,8	22,9	32,7	43,2	54,2	100
	18,0	29,8	42,6	56,2	70,5	50
VB418x	16,2	26,8	38,4	50,7	63,6	100
	21,3	35,4	50,6	66,7	83,7	50

[1] ΔT is the temperature difference between the upper limiting temperature of the installed equipment and the ambient air temperature of the distribution board.

EN Safety instructions

Electrical devices must only be installed and assembled by a qualified electrician in accordance with the relevant installation standards, guidelines, regulations, directives, safety and accident prevention directives of the country.

Failure to comply with these installation instructions may result in damage to the device, fire or other dangers.

These instructions are an integral component of the product and must be retained by the end user.

The Assembly (DBO) designated markings must be completed as specified in IEC/EN 61439 - 3 clause 6.1.