



TXA111



Power supply 30V DC 320 mA

Technical Features

Capacity

| | |
|-------------------|---|
| Number of modules | 4 |
|-------------------|---|

Electric current

| | |
|----------------|--------|
| Output current | 320 mA |
|----------------|--------|

Connectivity

| | |
|---------------------------|----|
| With bus system KNX radio | No |
|---------------------------|----|

Voltage

| | |
|-------------------|-------------|
| Operating voltage | 230 - 230 V |
|-------------------|-------------|

| | |
|----------------|-----------|
| Output voltage | 28 - 32 V |
|----------------|-----------|

Connection

| | |
|----------------------------------|----------------------------|
| Cross-section flexible conductor | 0.75 - 2.5 mm ² |
|----------------------------------|----------------------------|

| | |
|-------------------------------|----------------------------|
| Cross-section rigid conductor | 0.75 - 2.5 mm ² |
|-------------------------------|----------------------------|

Use conditions

| | |
|-----------------------|------------|
| Operating temperature | -5 - 45 °C |
|-----------------------|------------|

Connectivity

| | |
|--------------------|--------------|
| Type of connection | quickconnect |
|--------------------|--------------|

Frequency

| | |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

Texts

| | |
|------|---|
| Fuse | With electronic short-circuit and overload protection |
|------|---|

| | |
|----------|---|
| Junction | Protected earth conductor must be connected |
|----------|---|

| | |
|--------------------|-------------------------------------|
| Type of connection | With quickconnect plug-in terminals |
|--------------------|-------------------------------------|

Power supply

| | |
|----------------|----------|
| Supply voltage | 230 V AC |
|----------------|----------|

Dimensions

| | |
|-----------------------|---|
| Number of width units | 4 |
|-----------------------|---|

Sustainability

| | |
|--------------|-----|
| Halogen free | Yes |
|--------------|-----|

| | |
|-----------------|-----|
| REACH-SVHC free | Yes |
|-----------------|-----|

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|