



NF206A

**MCB 2P 6/10kA C-6A 2M**

**Technical Features**

**Electric current**

|                       |        |
|-----------------------|--------|
| Rated current         | 6 A    |
| Rated current -15°C   | 7 A    |
| Rated current -10°C   | 6.90 A |
| Rated current -5°C    | 6.80 A |
| Rated current at 0°C  | 6.70 A |
| Rated current 5°C     | 6.60 A |
| Rated current 10°C    | 6.50 A |
| Rated current 15°C    | 6.30 A |
| Rated current at 20°C | 6.20 A |
| Rated current 25°C    | 6.10 A |
| Rated current 30°C    | 6 A    |
| Rated current 35°C    | 5.90 A |
| Rated current at 40°C | 5.80 A |
| Rated current at 45°C | 5.60 A |
| Rated current at 50°C | 5.50 A |
| Rated current 55°C    | 5.40 A |
| Rated current 60°C    | 5.20 A |
| Rated current 65°C    | 5.10 A |
| Rated current 70°C    | 5 A    |

**Architecture**

|              |    |
|--------------|----|
| Type of pole | 2P |
| Curve        | C  |

**Capacity**

|                   |   |
|-------------------|---|
| Number of modules | 2 |
|-------------------|---|

**Main electrical attributes**

|                                                                                   |      |
|-----------------------------------------------------------------------------------|------|
| Rated short-circuit breaking capacity I <sub>cn</sub> AC according to IEC 60898-1 | 6 kA |
|-----------------------------------------------------------------------------------|------|

**Installation, mounting**

|                                         |                |
|-----------------------------------------|----------------|
| Nominal tightening torque top terminal  | 2.80 - 2.80 Nm |
| Nominal tightening torque down terminal | 2.80 - 2.80 Nm |

**Voltage**

|                                                  |             |
|--------------------------------------------------|-------------|
| Rated operational voltage U <sub>e</sub>         | 400 - 400 V |
| Rated insulation voltage U <sub>i</sub>          | 500 V       |
| Rated impulse withstand voltage U <sub>imp</sub> | 4000 V      |

**Frequency**

|           |            |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

**Connection**

|                                                                        |                        |
|------------------------------------------------------------------------|------------------------|
| Cross-section of input and output with screws, for massive conductors  | 1 - 35 mm <sup>2</sup> |
| Cross-section of input and output with screws, for flexible conductors | 1 - 25 mm <sup>2</sup> |
| Cross-section of input with screws, for flexible conductors            | 1 - 25 mm <sup>2</sup> |
| Cross-section of input with screws, for massive conductors             | 1 - 35 mm <sup>2</sup> |

**Installation, mounting**

|                                               |                |
|-----------------------------------------------|----------------|
| Nominal tightening torque                     | 2.80 - 2.80 Nm |
| Type of bottom connection for modular devices | biconnect      |
| Type of top connection for modular devices    | Screw terminal |
| 360° mounting position possible               | Yes            |

**Safety**

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

---

**Use conditions**

|                                                          |                  |
|----------------------------------------------------------|------------------|
| Degree of pollution according to IEC 60664 / IEC 60947-2 | 2                |
| Class of energy limitation I <sup>2</sup> t              | 3                |
| Air humidity protection                                  | For all climates |
| Operating temperature                                    | -25 - 70 °C      |

**Power**

|                           |        |
|---------------------------|--------|
| Total power loss under IN | 2.60 W |
|---------------------------|--------|

**Connectivity**

|                                               |                  |
|-----------------------------------------------|------------------|
| Type of connection                            | Screw terminal   |
| Top connection alignment for modular devices  | Aligned terminal |
| Down connection alignment for modular devices | Aligned terminal |

**Dimensions**

|        |       |
|--------|-------|
| Height | 83 mm |
| Width  | 35 mm |
| Depth  | 70 mm |

**Sustainability**

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|