



EMN005

**Multifunction stair case time lag switch**

**Technical Features**

**Frequency**

Frequency 50 - 60 Hz

**Electric current**

Rated current 16 A

**Capacity**

Number of modules 1

**Connectivity**

Type of connection Screw terminal  
Wire connection

**Installation, mounting**

Mounting on DIN rail

**Lighting**

Max. load fluorescent lamp parallel compensated 1000 VA

Max. load fluorescent lamp 3600 VA

**Use conditions**

Operating temperature -10 - 55 °C

**Connection**

Cross-section flexible conductor 1 - 6 mm<sup>2</sup>

Cross-section rigid conductor 1.5 - 10 mm<sup>2</sup>

**Settings**

Time delay 30 S - 10 Min

**Dimensions**

Width 17.50 mm

Depth 64 mm