



EMN001



IP20



Stair case time lag switch

Technical Features

Voltage

Rated operational voltage U _e	230 - 230 V
--	-------------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Electric current

Rated current	16 A
---------------	------

Capacity

Number of modules	1
-------------------	---

Connectivity

Type of connection	Screw terminal Wire connection
--------------------	-----------------------------------

Installation, mounting

Mounting on	DIN rail
-------------	----------

Lighting

Max. load fluorescent lamp parallel compensated	1000 VA
---	---------

Max. load fluorescent lamp	3600 VA
----------------------------	---------

Use conditions

Operating temperature	-10 - 55 °C
-----------------------	-------------

Connection

Cross-section flexible conductor	1 - 6 mm ²
----------------------------------	-----------------------

Cross-section rigid conductor	1.5 - 10 mm ²
-------------------------------	--------------------------

Settings

Time delay	30 S - 10 Min
------------	---------------

Dimensions

Width	17.50 mm
-------	----------

Depth	64 mm
-------	-------

Power

230 V incandescent and halogen lamp	2300 W
-------------------------------------	--------

Texts

Junction	For 3 and 4-conductor circuit (automatic detection)
----------	---

Switch mode	NO contact
-------------	------------

Installation mode	For mounting on DIN rail
-------------------	--------------------------

Type of connection	With screw terminals
--------------------	----------------------

Sustainability

RoHS conform	Yes
--------------	-----