



SB425

Switch 4X25A 400V POS IND

Technical Features

Architecture

Number of poles	4
Type of pole	4P

Electric current

Rated current	25 A
Rated conditional short-circuit current Icc with gl-gG fuses	10 kA
Acceptable current rating AC22 category A	25 A

Installation, mounting

Nominal tightening torque	2.90 - 2.90 Nm
---------------------------	----------------

Voltage

Type voltage supply	AC
Rated insulation voltage Ui	500 V
Rated impulse withstand voltage Uimp	3000 V

Capacity

Number of modules	2
-------------------	---

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Dimensions

Height	85 mm
Width	36 mm
Depth	72 mm
Dimensions	85 x 36 mm

Equipment

Number of NO contacts	4
Number of NC contacts	0

Use conditions

Operating temperature	-10 - 50 °C
Storage/transport temperature	-40 - 80 °C

Connection

Cross-section flexible conductor	10 mm ²
Cross-section rigid conductor	16 mm ²

Endurance

Number of mechanical operations	150000
Electrical durability at nominal load in AC22 in operating cycles	30000

Power

Total power loss under IN	3.60 W
---------------------------	--------

Illustrations | Drawings

