



52303213

On/off switch 2pole earthing contact, light control

Technical Features

Electric current	
Switching current	20 AX (200W LED (SBL))
Installation, mounting	
Mounting on	Flush mounting
Voltage	
Rated voltage	250 V
Frequency	
Frequency	50 - 60 Hz
Materials	
Material	Metal Plastic
Treatment	Untreated
Identification	
Assembly arrangement	Basic element
Connectivity	
Mounting type	Clamp mounting Screw connection
Controls and indicators	
Number of buttons	1
Dimensions	
Dimensions	71 x 71 mm
Built-in depth	31 mm
Built-in depth flush-mounted boxes	35 mm
Safety	
Ingress Protection (IP) class	IP20
Architecture	
Control/operation element	Single rocker
Electric current	
Rated current	20 A
Texts	
Type of connection	With screw terminals
Lighting	With neon lamp unit For lighting and monitoring circuit
Switch mode	2-pole off
Sustainability	
RoHS conform	Yes