



WMPS12WG

10AX 1 Gang 2 Way Switch Wide Rocker Grey

Technical Features

Electric current

| | |
|-------------------|------|
| Switching current | 10 A |
|-------------------|------|

Installation, mounting

| | |
|-------------|----------------|
| Mounting on | Flush mounting |
|-------------|----------------|

Voltage

| | |
|---------------|-------|
| Rated voltage | 250 V |
|---------------|-------|

Materials

| | |
|----------------|-------------------|
| Colour | Grey |
| Surface finish | Glossy |
| Material | Urea formaldehyde |
| Treatment | Untreated |

Identification

| | |
|----------------------|-------------------------------------|
| Assembly arrangement | Basic element with full cover plate |
|----------------------|-------------------------------------|

Connectivity

| | |
|---------------|----------------|
| Mounting type | Screw mounting |
|---------------|----------------|

Controls and indicators

| | |
|-------------------|---|
| Number of buttons | 1 |
|-------------------|---|

Dimensions

| | |
|----------------|------------|
| Dimensions | 86 x 86 mm |
| Built-in depth | 12 mm |

Safety

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP21 |
|-------------------------------|------|

Architecture

| | |
|---------------------------|---------------|
| Control/operation element | Single rocker |
|---------------------------|---------------|

Electric current

| | |
|---------------|------|
| Rated current | 10 A |
|---------------|------|

Texts

| | |
|-------------------|--|
| Installation mode | For flush-mounted and hollow wall mounting |
| Lighting | Without lighting (cannot be illuminated) |
| Switch mode | 2-way, with loop terminal |

Sustainability

| | |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform | Yes |