



AD910J

### RCBO 1P+N 6kA B-10A 30mA A Class

#### Technical Features

##### Architecture

Type of pole	1P+N
Curve	B

##### Electric current

Rated current	10 A
Rated residual operating current Idn	30 mA
Rated current -25°C	12 A
Rated current at -20°C	11.80 A
Rated current -15°C	11.70 A
Rated current -10°C	11.50 A
Rated current -5°C	11.30 A
Rated current at 0°C	11.10 A
Rated current 5°C	11 A
Rated current 10°C	10.80 A
Rated current 15°C	10.60 A
Rated current at 20°C	10.40 A
Rated current 25°C	10.20 A
Rated current 30°C	10 A
Rated current 35°C	9.90 A
Rated current at 40°C	9.70 A
Rated current at 50°C	9.40 A
Rated current 55°C	9.30 A
Rated current 60°C	9.10 A
Correction factor of rating current for 2 devices placed side by side	1
Correction factor of rating current for 3 devices placed side by side	0.95
Correction factor of rating current for 4 and 5 devices placed side by side	0.90
Correction factor of rating current for 6 devices placed side by side	0.85
Min./max. threshold value of the AC thermal operation	1.13 - 1.45 A
Rated short-circuit breaking capacity Icn under 230 V AC according to IEC 60898-1	6 kA

##### Safety

Residual current type	A
Ingress Protection (IP) class	IP2X

##### Main electrical attributes

Rated short-circuit breaking capacity Icn AC according to IEC 60898-1	6 kA
---	------

##### Connectivity

Type of connection	Screw terminal
--------------------	----------------

##### Voltage

Rated insulation voltage Ui	500 V
Rated impulse withstand voltage Uimp	4000 V
Max. operating voltage	240 V
Rated operational voltage Ue	240 - 240 V
Overvoltage category according to IEC 60947-1	3

##### Power

Total power loss under IN	3.40 W
---------------------------	--------

##### Frequency

Frequency	50 - 50 Hz
-----------	------------

##### Use conditions

Max. Altitude	2000 m
Class of energy limitation I <sup>2</sup> t	3

# Product Datasheet

## AD910J

---

### Endurance

Electric endurance in number of cycles	2000
Number of mechanical operations	2000

### Connection

Cross-section flexible conductor	1 - 16 mm <sup>2</sup>
Cross-section rigid conductor	1 - 25 mm <sup>2</sup>
Cross-section of input with screws, for flexible conductors	1 - 16 mm <sup>2</sup>
Cross-section of input with screws, for massive conductors	1 - 25 mm <sup>2</sup>
Cross-section of output with screws, for flexible conductors	1 - 16 mm <sup>2</sup>
Cross-section of output with screws, for massive conductors	1 - 25 mm <sup>2</sup>

### Installation, mounting

Nominal tightening torque	2.10 - 2.10 Nm
---------------------------	----------------

### Capacity

Number of modules	2
-------------------	---

### Installation, mounting

Type of top connection for modular devices	Screw terminal
Type of bottom connection for modular devices	biconnect

### Dimensions

Height	83 mm
Width	35 mm
Depth	68 mm

### Use conditions

Operating temperature	-25 - 40 °C
Storage/transport temperature	-25 - 70 °C

### Connection

Cross-section of input and output with screws, for flexible conductors	1 - 16 mm <sup>2</sup>
Cross-section of input and output with screws, for massive conductors	1 - 25 mm <sup>2</sup>

### Sustainability

RoHS conform	Yes
--------------	-----