



FWB42M2

FWB encl. univers,IP44,class II, 4x26mod.,650x550x161mm,QuickConnect

### Technical Features

#### Installation, mounting

Suitable for outdoor usage	No
Mounting on	Surface mounting

#### Electric current

Rated current	125 A
---------------	-------

#### Equipment

Number of rails	4
Number of rows	4
Number of section in width	2
With lock	No
Has neutral terminal block	No

#### Capacity

Number of modules	104
-------------------	-----

#### Functions

With conduit inlets	Yes
---------------------	-----

#### Dimensions

Height	650 mm
Width	550 mm
Depth	165 mm

#### Cover, door

Number of cabinet doors	1
Number of locks	0

#### Dimensions

Number of width units	26
-----------------------	----

#### Cover, door

Type of handle	Hinged pattern handle
Door/cover is transparent	No

#### Connection

Number of conduit inlets	8
--------------------------	---

#### Materials

Material	Steel
RAL code	9010
Colour	Pure white

#### Equipment

Has earthing terminal block	No
Has mounting plate	No

#### Safety

Protection class	Isolation class II
Impact resistance IK	IK09
Ingress Protection (IP) class	IP44
Locking type	Bar lock

#### Sustainability

RoHS conform	Yes
--------------	-----