



MLN716A

**MCB 1P+N 6kA C-16A 1M**

**Technical Features**

**Architecture**

Type of pole	1P+N
Curve	C

**Electric current**

Rated current	16 A
Rated service breaking capacity Ics AC according to IEC 60898-1	6 kA
Rated short-circuit breaking capacity Icn under 230 V AC according to IEC 60898-1	6 kA
Min./max. threshold value of the AC thermal operation	1.13 - 1.45 A
Min./max. threshold value of the DC thermal operation	1.13 - 1.45 A
Rated current -25°C	19.70 A
Rated current at -20°C	19.40 A
Rated current -15°C	19.10 A
Rated current -10°C	18.80 A
Rated current -5°C	18.50 A
Rated current at 0°C	18.10 A
Rated current 5°C	17.80 A
Rated current 10°C	17.50 A
Rated current 15°C	17.10 A
Rated current at 20°C	16.70 A
Rated current 25°C	16.40 A
Rated current 30°C	16 A
Rated current 35°C	15.60 A
Rated current at 40°C	15.20 A
Rated current at 45°C	14.80 A
Rated current at 50°C	14.40 A
Rated current 55°C	14 A
Rated current 60°C	13.50 A
Rated current 65°C	13.10 A
Rated current 70°C	12.60 A
Correction factor of rating current for 2 devices placed side by side	1
Correction factor of rating current for 3 devices placed side by side	0.95
Correction factor of rating current for 4 and 5 devices placed side by side	0.90
Correction factor of rating current for 6 devices placed side by side	0.85

**Main electrical attributes**

Rated short-circuit breaking capacity Icn AC according to IEC 60898-1	6 kA
---	------

**Installation, mounting**

Nominal tightening torque down terminal	1.90 - 1.90 Nm
Nominal tightening torque top terminal	1.90 - 1.90 Nm

**Voltage**

Rated operational voltage Ue	230 - 240 V
Type voltage supply	AC
Rated insulation voltage Ui	500 V
Rated impulse withstand voltage Uimp	4000 V
Max. operating voltage	253 V
Overvoltage category according to IEC 60947-1	3

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Capacity**

Number of modules	1
-------------------	---

**Installation, mounting**

Type of top connection for modular devices	Screw terminal
--	----------------

---

**Installation, mounting**

Type of bottom connection for modular devices	Screw terminal
Nominal tightening torque	1.90 - 1.90 Nm

---

**Connection**

Cross-section of input with screws, for massive conductors	1 - 25 mm <sup>2</sup>
Cross-section of input with screws, for flexible conductors	1 - 16 mm <sup>2</sup>

---

**Power**

Total power loss under IN	4.40 W
---------------------------	--------

---

**Use conditions**

Operating temperature	-25 - 70 °C
Max. Altitude	2000 m

---

**Endurance**

Electric endurance in number of cycles	1000
Number of mechanical operations	20000

---

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

---

**Connectivity**

Type of connection	Screw terminal
Top connection alignment for modular devices	Shifted terminal
Down connection alignment for modular devices	Shifted terminal

---

**Dimensions**

Height	84.70 mm
Width	17.50 mm
Depth	70 mm

---

**Sustainability**

RoHS conform	Yes
--------------	-----