



HNB200Z

### Moulded Case Circuit Breaker x250 3P 40kA 200A TM

#### Technical Features

##### Electric current

|                                                                               |          |
|-------------------------------------------------------------------------------|----------|
| Rated current                                                                 | 200 A    |
| Rated ultimate short-circuit breaking capacity Icu under 400 V AC IEC 60947-2 | 40 kA    |
| Rated ultimate short-circuit breaking capacity Icu under 240 V AC IEC 60947-2 | 85 kA    |
| Rated current 10°C according to IEC 60947                                     | 238 A    |
| Rated current 15°C according to IEC 60947                                     | 233.60 A |
| Rated current 20°C according to IEC 60947                                     | 229.20 A |
| Rated current 25°C according to IEC 60947                                     | 224.60 A |
| Rated current 30°C according to IEC 60947                                     | 219.80 A |
| Rated current at 35°C according to IEC 60947                                  | 215 A    |
| Rated current at 40°C according to IEC 60947                                  | 210.20 A |
| Rated current 45°C according to IEC 60947                                     | 205 A    |
| Rated current 50°C according to IEC 60947                                     | 200 A    |
| Rated current 55°C according to IEC 60947                                     | 194.80 A |
| Rated current at 60°C according to IEC 60947                                  | 189.20 A |
| Rated current 65°C according to IEC 60947                                     | 183.80 A |
| Rated current 70°C according to IEC 60947                                     | 178.20 A |

##### Architecture

|                           |                |
|---------------------------|----------------|
| Number of poles           | 3              |
| Control/operation element | Toggle         |
| Device construction type  | Fixed built-in |

##### Tripping

|                            |       |
|----------------------------|-------|
| Response time when opening | 10 ms |
|----------------------------|-------|

##### Frequency

|           |            |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

##### Voltage

|                                      |        |
|--------------------------------------|--------|
| Rated impulse withstand voltage Uimp | 8000 V |
| Rated insulation voltage Ui          | 800 V  |

##### Functions

|           |        |
|-----------|--------|
| Trip unit | TM F/F |
|-----------|--------|

##### Power

|                           |         |
|---------------------------|---------|
| Total power loss under IN | 38.40 W |
|---------------------------|---------|

##### Endurance

|                                        |      |
|----------------------------------------|------|
| Electric endurance in number of cycles | 1000 |
| Number of mechanical operations        | 4000 |

##### Safety

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP4X |
|-------------------------------|------|

##### Connection

|                                  |                          |
|----------------------------------|--------------------------|
| Cross-section flexible conductor | 35 - 150 mm <sup>2</sup> |
| Cross-section rigid conductor    | 35 - 185 mm <sup>2</sup> |

##### Installation, mounting

|                               |            |
|-------------------------------|------------|
| Nominal tightening torque     | 12 - 12 Nm |
| Mounting-/Connection Position | Front      |

##### Settings

|                                                           |         |
|-----------------------------------------------------------|---------|
| Thermal protection knob setting xIN                       | 1       |
|                                                           | 1       |
| Adjustment range short-term delayed short-circuit release | 0 - 0 A |

|                                   |          |
|-----------------------------------|----------|
| <b>Compatibility</b>              |          |
| Suitable for DIN Rail             | No       |
| <b>Main electrical attributes</b> |          |
| Magnetic protection trip time     | 0 - 0 ms |
| <b>Sustainability</b>             |          |
| REACH-SVHC free                   | Yes      |
| RoHS conform                      | Yes      |