



SH363S

One piece switch 3x63A + additional cage & padlockable

Technical Features

Electric current

Rated current	63 A
Rated conditional short-circuit current I_{nc} with fuse according to IEC/EN 60669-2-4	6000A/63A gG

Architecture

Type of pole	3P
Control/operation element	Toggle
Neutral position	Without neutral
Number of poles	3

Connection

Cross-section rigid conductor	25 mm ²
-------------------------------	--------------------

Voltage

Rated insulation voltage U_i	500 V
Rated impulse withstand voltage U_{imp}	6 kV
Rated operational voltage U_e	400 - 400 V
Type voltage supply	AC

Power

Power loss per pole at I_n	2.60 W
Total power loss under I_N	7.80 W

Installation, mounting

Nominal tightening torque	2 - 2 Nm
---------------------------	----------

Equipment

Motor drive optional	No
Number of auxiliary contacts as change-over contact	0
Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0

Use conditions

Operating temperature	-5 - 40 °C
-----------------------	------------

Cover, door

Interlockable	No
---------------	----

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Frequency

Frequency	50 - 50 Hz
-----------	------------

Connectivity

Type of connection	Screw terminal
--------------------	----------------

Functions

Is reversing switch	No
Version as emergency stop installation	No
Version as main switch	Yes
Version as maintenance/service switch	Yes
Version as safety switch	No
Version as switch disconnecter compact	Yes

Equipment

Sealable	Yes
----------	-----

Capacity

Number of modules	2.50
-------------------	------

Sustainability

Halogen free	Yes
RoHS conform	Yes

Illustrations | Drawings

