



WGDL111P

10A 1G press switch

Technical Features

Electric current

| | |
|-------------------|------|
| Switching current | 10 A |
|-------------------|------|

Voltage

| | |
|---------------|-------|
| Rated voltage | 250 V |
|---------------|-------|

Architecture

| | |
|---------------------------|---------------|
| Control/operation element | Single rocker |
|---------------------------|---------------|

Materials

| | |
|--------|-------|
| Colour | White |
|--------|-------|

| | |
|----------------|--------|
| Surface finish | Glossy |
|----------------|--------|

| | |
|----------|--------------------|
| Material | Polycarbonate (PC) |
|----------|--------------------|

| | |
|-----------|-----------|
| Treatment | Untreated |
|-----------|-----------|

| | |
|-------------|----|
| Transparent | No |
|-------------|----|

Dimensions

| | |
|--------|-------|
| Height | 86 mm |
|--------|-------|

| | |
|-------|-------|
| Width | 86 mm |
|-------|-------|

| | |
|-------|-------|
| Depth | 25 mm |
|-------|-------|

| | |
|------------------------------------|-------|
| Built-in depth flush-mounted boxes | 35 mm |
|------------------------------------|-------|

Controls and indicators

| | |
|-------------------|---|
| Number of buttons | 1 |
|-------------------|---|

| | |
|------------------------------|----|
| With feedback signal contact | No |
|------------------------------|----|

Connectivity

| | |
|--------------------|----------------|
| Type of connection | Screw terminal |
|--------------------|----------------|

Safety

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

Accessories

| | |
|---------------------|----|
| Has labelling field | No |
|---------------------|----|

Texts

| | |
|-------------|-------|
| Switch mode | 1-way |
|-------------|-------|

Suitable for

| | |
|-------|--|
| shark | |
|-------|--|

Sustainability

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|