



HNA020Z

**Moulded Case Circuit Breaker h3 x160 TM FIX 3P3D 20A 40kA CTC**

**Technical Features**

**Electric current**

Rated current	20 A
Rated ultimate short-circuit breaking capacity I <sub>cu</sub> under 400 V AC IEC 60947-2	40 kA
Rated ultimate short-circuit breaking capacity I <sub>cu</sub> under 240 V AC IEC 60947-2	85 kA
Rated service breaking capacity I <sub>cs</sub> under 230 V AC according to IEC 60947-2	40 kA
Rated service breaking capacity I <sub>cs</sub> under 400 V AC according to IEC 60947-2	20 kA
Rated current 10°C according to IEC 60947	24,90 A
Rated current 15°C according to IEC 60947	24,40 A
Rated current 20°C according to IEC 60947	23,80 A
Rated current 25°C according to IEC 60947	23,20 A
Rated current 30°C according to IEC 60947	22,60 A
Rated current at 35°C according to IEC 60947	22 A
Rated current at 40°C according to IEC 60947	21,30 A
Rated current 45°C according to IEC 60947	20,60 A
Rated current 50°C according to IEC 60947	20 A
Rated current 55°C according to IEC 60947	19,20 A
Rated current at 60°C according to IEC 60947	18,50 A
Rated current 65°C according to IEC 60947	17,70 A
Rated current 70°C according to IEC 60947	16,90 A

**Architecture**

Number of poles	3
Neutral position	Without neutral

**Tripping**

Response time when opening	10 ms
----------------------------	-------

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Voltage**

Rated impulse withstand voltage U <sub>imp</sub>	8000 V
Rated insulation voltage U <sub>i</sub>	690 V
Rated operational voltage U <sub>e</sub>	220 - 415 V

**Functions**

Trip unit	TM F/F
-----------	--------

**Power**

Total power loss under I <sub>N</sub>	8,70 W
---------------------------------------	--------

**Endurance**

Electric endurance in number of cycles	10000
Number of mechanical operations	20000

**Safety**

Ingress Protection (IP) class	IP4X
-------------------------------	------

**Connection**

Cross-section flexible conductor	4 - 70 mm <sup>2</sup>
Cross-section rigid conductor	4 - 95 mm <sup>2</sup>

**Connectivity**

Type of connection	Screw terminal
--------------------	----------------

**Settings**

Thermal protection knob setting xI <sub>N</sub>	1
	1

---

**Dimensions**

Height	130 mm
Width	75 mm
Depth	68 mm

**Compatibility**

Suitable for DIN Rail	No
-----------------------	----

**Main electrical attributes**

Magnetic protection trip time	0 - 0 ms
-------------------------------	----------

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes