



MCN402

### MCB 4P 6kA C-2A 4M

#### Technical Features

##### Electric current

Rated current	2 A
Rated ultimate short-circuit breaking capacity Icu under 400 V AC IEC 60947-2	10 kA
Rated current -15°C	2.5 A
Rated current -10°C	2.5 A
Rated current -5°C	2.4 A
Rated current at 0°C	2.4 A
Rated current 5°C	2.3 A
Rated current 10°C	2.2 A
Rated current 15°C	2.2 A
Rated current at 20°C	2.1 A
Rated current 25°C	2.1 A
Rated current 30°C	2 A
Rated current 35°C	1.9 A
Rated current at 40°C	1.9 A
Rated current at 45°C	1.8 A
Rated current at 50°C	1.7 A
Rated current 55°C	1.6 A
Rated current 60°C	1.5 A
Rated current 65°C	1.4 A
Rated current 70°C	1.4 A

##### Architecture

Type of pole	4P
Curve	C

##### Capacity

Number of modules	4
-------------------	---

##### Main electrical attributes

Rated short-circuit breaking capacity Icn AC according to IEC 60898-1	6 kA
---	------

##### Installation, mounting

Nominal tightening torque top terminal	2.80 - 2.80 Nm
Nominal tightening torque down terminal	2.80 - 2.80 Nm

##### Voltage

Rated operational voltage Ue	415 - 415 V
Type voltage supply	AC
Rated insulation voltage Ui	500 V
Rated impulse withstand voltage Uimp	4000 V

##### Frequency

Frequency	50 - 60 Hz
-----------	------------

##### Connection

Cross-section of input and output with screws, for massive conductors	1 - 35 mm <sup>2</sup>
Cross-section of input and output with screws, for flexible conductors	1 - 25 mm <sup>2</sup>
Cross-section of input with screws, for flexible conductors	1 - 25 mm <sup>2</sup>
Cross-section of input with screws, for massive conductors	1 - 35 mm <sup>2</sup>
Cross-section flexible conductor	1 - 25 mm <sup>2</sup>
Cross-section rigid conductor	1 - 35 mm <sup>2</sup>

##### Installation, mounting

Nominal tightening torque	2.80 - 2.80 Nm
Type of bottom connection for modular devices	biconnect
Type of top connection for modular devices	Screw terminal
360° mounting position possible	Yes

# Product Datasheet

## MCN402

### Safety

Ingress Protection (IP) class

IP20

### Use conditions

Degree of pollution according to IEC 60664 / IEC 60947-2

2

Class of energy limitation  $I^2t$

3

Air humidity protection

For all climates

Operating temperature

-25 - 70 °C

### Power

Total power loss under IN

5.40 W

### Connectivity

Type of connection

Screw terminal

Top connection alignment for modular devices

Aligned terminal

Down connection alignment for modular devices

Aligned terminal

### Dimensions

Height

84.60 mm

Width

70 mm

Depth

70 mm

### Sustainability

RoHS conform

Yes

### Illustrations | Drawings

