



MZ201

Auxiliary contact 1C+1O 6A 240V AC

Technical Features

Electric current

| | |
|---------------|-----|
| Rated current | 6 A |
|---------------|-----|

Connectivity

| | |
|--------------------|----------------|
| Type of connection | Screw terminal |
| Mounting type | Click mounting |

Capacity

| | |
|-------------------|------|
| Number of modules | 0.50 |
|-------------------|------|

Connection

| | |
|----------------------------------|--------------------|
| Type of contacts | 1NC+1NO |
| Cross-section flexible conductor | 6 mm ² |
| Cross-section rigid conductor | 10 mm ² |

Voltage

| | |
|-----------------------------|--------|
| Rated insulation voltage Ui | 4000 V |
| Type voltage supply | AC |

Endurance

| | |
|---------------------------------|-------|
| Number of mechanical operations | 12000 |
|---------------------------------|-------|

Use conditions

| | |
|-----------------------|-------------|
| Operating temperature | -25 - 60 °C |
|-----------------------|-------------|

Endurance

| | |
|--|------|
| Electric endurance in number of cycles | 6000 |
|--|------|

Use conditions

| | |
|-------------------------------|-------------|
| Storage/transport temperature | -40 - 80 °C |
|-------------------------------|-------------|

Power

| | |
|---------------------------|--------|
| Total power loss under IN | 0.10 W |
|---------------------------|--------|

Dimensions

| | |
|--------|---------|
| Height | 80 mm |
| Width | 9.50 mm |
| Depth | 40 mm |

Equipment

| | |
|------------------------|---|
| Number of INV contacts | 0 |
| Number of NC contacts | 1 |

Sustainability

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|

Illustrations | Drawings

