



NF216A

**MCB 2P 6/10kA C-16A 2M**

**Technical Features**

**Electric current**

Rated current	16 A
Rated current -15°C	19.30 A
Rated current -10°C	19 A
Rated current -5°C	18.60 A
Rated current at 0°C	18.30 A
Rated current 5°C	17.90 A
Rated current 10°C	17.60 A
Rated current 15°C	17.20 A
Rated current at 20°C	16.80 A
Rated current 25°C	16.40 A
Rated current 30°C	16 A
Rated current 35°C	15.60 A
Rated current at 40°C	15.20 A
Rated current at 45°C	14.70 A
Rated current at 50°C	14.30 A
Rated current 55°C	13.80 A
Rated current 60°C	13.30 A
Rated current 65°C	12.90 A
Rated current 70°C	12.40 A

**Architecture**

Type of pole	2P
Curve	C

**Capacity**

Number of modules	2
-------------------	---

**Main electrical attributes**

Rated short-circuit breaking capacity Icn AC according to IEC 60898-1	6 kA
---	------

**Installation, mounting**

Nominal tightening torque top terminal	2.80 - 2.80 Nm
Nominal tightening torque down terminal	2.80 - 2.80 Nm

**Voltage**

Rated operational voltage Ue	400 - 400 V
Rated insulation voltage Ui	500 V
Rated impulse withstand voltage Uimp	4000 V

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Connection**

Cross-section of input and output with screws, for massive conductors	1 - 35 mm <sup>2</sup>
Cross-section of input and output with screws, for flexible conductors	1 - 25 mm <sup>2</sup>
Cross-section of input with screws, for flexible conductors	1 - 25 mm <sup>2</sup>
Cross-section of input with screws, for massive conductors	1 - 35 mm <sup>2</sup>

**Installation, mounting**

Nominal tightening torque	2.80 - 2.80 Nm
Type of bottom connection for modular devices	biconnect
Type of top connection for modular devices	Screw terminal
360° mounting position possible	Yes

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

---

**Use conditions**

Degree of pollution according to IEC 60664 / IEC 60947-2	2
Class of energy limitation I <sup>2</sup> t	3
Air humidity protection	For all climates
Operating temperature	-25 - 70 °C

**Power**

Total power loss under IN	5.10 W
---------------------------	--------

**Connectivity**

Type of connection	Screw terminal
Top connection alignment for modular devices	Aligned terminal
Down connection alignment for modular devices	Aligned terminal

**Dimensions**

Height	83 mm
Width	35 mm
Depth	70 mm

**Sustainability**

RoHS conform	Yes
--------------	-----