



REN230X



Transponder reader module built-in stainless steel matt modesta

Technical Features

Dimensions

Height	120 mm
Width	120 mm
Depth	31 mm
Dimensions	120 x 120 mm

Materials

Colour	Stainless steel
Treatment	Brushed
Material	Metal Stainless steel

Equipment

Number of simultaneous access Ids	200
Contact less	Yes
Stand-alone	Yes

Voltage

Operating voltage at AC 50 Hz	12 - 15 V
Operating voltage at AC 60 Hz	12 - 15 V
Operating voltage DC	12 - 24 V

Texts

Installation mode	Mounting in MODESTA frame
Junction	Potential-free changeover contact 24 V/1 A
Main functions	Access control via RFID transponder Selective deleting of single ID cards Stand-alone operation without further control unit Memory slot for up to 200 ID cards/transponders
Reader unit	Behind flush-fitting acrylic glass pane Wound "radio key" symbol 2x digit LED display for indication of active storage space
Voltage	Without PoE power supply

Equipment

Change over contact potential free	max. 24V/1A
------------------------------------	-------------

Power

Current consumption	200 mA
---------------------	--------

Functions

Access control system	Transponder reader
-----------------------	--------------------

Connection

Conductor cross-section	0 - 0 mm ²
-------------------------	-----------------------

Connectivity

Connectable	No
-------------	----

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Use conditions

Operating temperature	-20 - 55 °C
-----------------------	-------------

Sustainability

RoHS conform	Yes
--------------	-----