



HA964N

Load break switch with visible breaking 4P 250A

Technical Features

Electric current

Rated current	250 A
Acceptable current rating AC21	250 A
Acceptable current rating AC21 category A	250 A
Acceptable current rating AC21 category B	250 A
Acceptable current rating AC22 category A	250 A
Acceptable current rating AC22 category B	250 A
Acceptable current rating AC23 category A	200 A
Acceptable current rating AC23 category B	200 A
Rated short-circuit making capacity I _{cm} under 415 V AC according to IEC 60947-3	15.30 kA
Rated short-time withstand current I _{cw} 1s IEC 60947	9 kA
Rated short-time withstand current I _{cw} IEC 60947	9 kA

Architecture

Type of pole	4P
Number of poles	4

Connection

Cross-section rigid conductor	150 mm ²
Cross-section flexible conductor	150 mm ²

Voltage

Rated insulation voltage U _i	800 V
Rated impulse withstand voltage U _{imp}	8000 V
Rated operational voltage U _e	380 - 415 V

Power

Power loss per pole at I _n	19 W
Total power loss under I _N	76 W
Rated operational power under 400 V AC AC1	164000 W
Rated operational power under 400 V AC AC23	112000 W

Equipment

Motor drive optional	No
Number of auxiliary contacts as change-over contact	0
Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0

Cover, door

Interlockable	Yes
---------------	-----

Safety

Ingress Protection (IP) class	IP00
-------------------------------	------

Architecture

Control/operation element	Long rotary handle
---------------------------	--------------------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Functions

Is reversing switch	No
Version as emergency stop installation	No
Version as main switch	Yes
Version as maintenance/service switch	Yes
Version as safety switch	Yes
Version as switch disconnecter compact	Yes

Dimensions

Height	160 mm
Width	187 mm
Depth	162 mm

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes

Illustrations | Drawings

