



**SURFACE CNSMR UNIT 6 WAY W/S FOR AI SW**

**Technical Features**

**Voltage**

|                 |             |
|-----------------|-------------|
| Nominal voltage | 230 - 415 V |
|-----------------|-------------|

**Installation, mounting**

|                            |                  |
|----------------------------|------------------|
| Suitable for outdoor usage | No               |
| Mounting on                | Surface mounting |

**Equipment**

|                 |   |
|-----------------|---|
| Number of rails | 1 |
| Number of rows  | 1 |

**Capacity**

|                   |   |
|-------------------|---|
| Number of modules | 6 |
|-------------------|---|

**Dimensions**

|        |        |
|--------|--------|
| Height | 231 mm |
| Width  | 250 mm |
| Depth  | 93 mm  |

**Cover, door**

|                         |   |
|-------------------------|---|
| Number of cabinet doors | 1 |
|-------------------------|---|

**Dimensions**

|                |       |
|----------------|-------|
| Built-in depth | 71 mm |
|----------------|-------|

**Cover, door**

|                 |   |
|-----------------|---|
| Number of locks | 0 |
|-----------------|---|

**Dimensions**

|                       |   |
|-----------------------|---|
| Number of width units | 6 |
|-----------------------|---|

**Cover, door**

|                           |    |
|---------------------------|----|
| Door/cover is transparent | No |
|---------------------------|----|

**Connection**

|                          |    |
|--------------------------|----|
| Number of conduit inlets | 10 |
|--------------------------|----|

**Connectivity**

|               |                |
|---------------|----------------|
| Mounting type | Screw mounting |
|---------------|----------------|

**Materials**

|          |            |
|----------|------------|
| Material | Steel      |
| RAL code | 9002       |
| Colour   | Grey white |

**Equipment**

|                    |    |
|--------------------|----|
| Has mounting plate | No |
|--------------------|----|

**Safety**

|                               |                   |
|-------------------------------|-------------------|
| Protection class              | Isolation class I |
| Impact resistance IK          | IK05              |
| Ingress Protection (IP) class | IP40              |
| Locking type                  | Without lock      |

**Sustainability**

|                |     |
|----------------|-----|
| RECh-SVHC free | Yes |
|----------------|-----|