

**MCB 3P 3kA B-25A 3M**

**Technical Features**

**Electric current**

Rated current	25 A
---------------	------

**Architecture**

Type of pole	3P
Curve	B

**Capacity**

Number of modules	3
-------------------	---

**Main electrical attributes**

Rated short-circuit breaking capacity Icn AC according to IEC 60898-1	3 kA
---	------

**Installation, mounting**

Nominal tightening torque top terminal	2.80 - 2.80 Nm
Nominal tightening torque down terminal	2.80 - 2.80 Nm

**Voltage**

Rated operational voltage Ue	230 - 400 V
Rated insulation voltage Ui	500 V
Rated impulse withstand voltage Uimp	4000 V

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Connection**

Cross-section of input and output with screws, for massive conductors	1 - 35 mm <sup>2</sup>
Cross-section of input and output with screws, for flexible conductors	1 - 25 mm <sup>2</sup>
Cross-section of input with screws, for flexible conductors	1 - 25 mm <sup>2</sup>
Cross-section of input with screws, for massive conductors	1 - 35 mm <sup>2</sup>

**Installation, mounting**

Nominal tightening torque	2.80 - 2.80 Nm
Type of bottom connection for modular devices	biconnect
Type of top connection for modular devices	Screw terminal
360° mounting position possible	Yes

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Use conditions**

Degree of pollution according to IEC 60664 / IEC 60947-2	2
Class of energy limitation I <sup>2</sup> t	3
Air humidity protection	For all climates
Operating temperature	-25 - 70 °C

**Power**

Total power loss under IN	9.50 W
---------------------------	--------

**Connectivity**

Type of connection	Screw terminal
Top connection alignment for modular devices	Aligned terminal
Down connection alignment for modular devices	Aligned terminal

**Dimensions**

Height	83 mm
Width	52.50 mm
Depth	70 mm

---

**Sustainability**

---

RoHS conform

Yes