



HHD400U

Moulded Case Circuit Breaker h400 3P 25kA 400A TM

Technical Features

Electric current

Rated current	400 A
---------------	-------

Architecture

Number of poles	3
-----------------	---

Electric current

Rated ultimate short-circuit breaking capacity I _{cu} under 400 V AC IEC 60947-2	25 kA
Rated ultimate short-circuit breaking capacity I _{cu} under 240 V AC IEC 60947-2	35 kA

Frequency

Frequency	50 - 60 Hz
-----------	------------

Voltage

Rated impulse withstand voltage U _{imp}	8000 V
Rated insulation voltage U _i	800 V

Functions

Trip unit	TM A/A
-----------	--------

Main electrical attributes

Magnetic protection trip time	0 - 0 ms
-------------------------------	----------

Power

Total power loss under I _N	75 W
---------------------------------------	------

Endurance

Electric endurance in number of cycles	1000
Number of mechanical operations	4000

Safety

Ingress Protection (IP) class	IP4X
-------------------------------	------

Use conditions

Operating temperature	-25 - 70 °C
-----------------------	-------------

Connection

Cross-section flexible conductor	35 - 240 mm ²
Cross-section rigid conductor	35 - 240 mm ²
Connector/plug type	Terminal

Installation, mounting

Nominal tightening torque	22 - 22 Nm
Mounting-/Connection Position	Front

Settings

Thermal protection knob setting xI _N	0.63 0.8 1
Adjustment range short-term delayed short-circuit release	0 - 0 A