



MY316E

MCB 3P 4.5kA C-16A 3M

Technical Features

Electric current

| | |
|---------------|------|
| Rated current | 16 A |
|---------------|------|

Architecture

| | |
|--------------|----|
| Type of pole | 3P |
| Curve | C |

Capacity

| | |
|-------------------|---|
| Number of modules | 3 |
|-------------------|---|

Main electrical attributes

| | |
|-----------------------------------------------------------------------|---------|
| Rated short-circuit breaking capacity Icn AC according to IEC 60898-1 | 4.50 kA |
|-----------------------------------------------------------------------|---------|

Installation, mounting

| | |
|-----------------------------------------|----------------|
| Nominal tightening torque top terminal | 2.80 - 2.80 Nm |
| Nominal tightening torque down terminal | 2.80 - 2.80 Nm |

Voltage

| | |
|--------------------------------------|-------------|
| Rated operational voltage Ue | 230 - 400 V |
| Type voltage supply | AC |
| Rated insulation voltage Ui | 500 V |
| Rated impulse withstand voltage Uimp | 4000 V |

Frequency

| | |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

Connection

| | |
|------------------------------------------------------------------------|------------------------|
| Cross-section of input and output with screws, for massive conductors | 1 - 35 mm ² |
| Cross-section of input and output with screws, for flexible conductors | 1 - 25 mm ² |
| Cross-section of input with screws, for flexible conductors | 1 - 25 mm ² |
| Cross-section of input with screws, for massive conductors | 1 - 35 mm ² |
| Cross-section flexible conductor | 1 - 25 mm ² |
| Cross-section rigid conductor | 1 - 35 mm ² |

Installation, mounting

| | |
|-----------------------------------------------|----------------|
| Nominal tightening torque | 2.80 - 2.80 Nm |
| Type of bottom connection for modular devices | biconnect |
| Type of top connection for modular devices | Screw terminal |
| 360° mounting position possible | Yes |

Safety

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

Use conditions

| | |
|----------------------------------------------------------|------------------|
| Degree of pollution according to IEC 60664 / IEC 60947-2 | 2 |
| Class of energy limitation I ² t | 3 |
| Air humidity protection | For all climates |
| Operating temperature | -25 - 70 °C |

Power

| | |
|---------------------------|-----|
| Total power loss under IN | 7 W |
|---------------------------|-----|

Connectivity

| | |
|-----------------------------------------------|------------------|
| Type of connection | Screw terminal |
| Top connection alignment for modular devices | Aligned terminal |
| Down connection alignment for modular devices | Aligned terminal |

Dimensions

| | |
|--------|----------|
| Height | 83 mm |
| Width | 52.50 mm |
| Depth | 70 mm |

Sustainability

| | |
|-----------------|-----|
| REACH-SVHC free | Yes |
|-----------------|-----|