



FWB52S

FWB encl.,univers,5-rows 120 modules cl.II IP44 w.plain door, 800x550x161mm,QC

### Technical Features

#### Installation, mounting

Suitable for outdoor usage	No
Mounting on	Surface mounting

#### Electric current

Rated current	125 A
---------------	-------

#### Equipment

Number of rails	10
Number of rows	5
Number of section in width	2
With lock	No
Has neutral terminal block	Yes

#### Capacity

Number of modules	120
-------------------	-----

#### Functions

Has protection main switch	No
With conduit inlets	Yes

#### Dimensions

Height	800 mm
Width	550 mm
Depth	165 mm

#### Cover, door

Number of cabinet doors	1
-------------------------	---

#### Dimensions

Built-in depth	161 mm
----------------	--------

#### Cover, door

Number of locks	1
-----------------	---

#### Dimensions

Number of width units	24
-----------------------	----

#### Cover, door

Type of handle	Hinged pattern handle
Door/cover is transparent	No

#### Connection

Number of conduit inlets	8
--------------------------	---

#### Connectivity

Mounting type	Surface mounting
---------------	------------------

#### Materials

Material	Steel
RAL code	9010
Colour	Pure white

#### Equipment

Has earthing terminal block	Yes
Has mounting plate	No

#### Safety

Protection class	Isolation class II
Impact resistance IK	IK09
Ingress Protection (IP) class	IP44

<b>Safety</b>	
Locking type	Without lock
Glow wire test	750 °C
<b>Sustainability</b>	
RoHS conform	Yes