



EH111



Time switch daily cycle with reserve 3 modules

Technical Features

Equipment

Number of channels 1

Frequency

Frequency 50 - 50 Hz

Power

Power consumption during operation 0.50 VA

230 V incandescent and halogen lamp 900 W

Power incandescent lamp 900 - 900 W

Functions

Number of function channels 1

Connection

Number of contacts 1

Cross-section flexible conductor 1 - 4 mm²

Cross-section rigid conductor 1 - 4 mm²

Use conditions

Operating temperature -10 - 45 °C

Capacity

Number of modules 3

Dimensions

Height 90 mm

Width 54 mm

Depth 60 mm

Texts

Switch mode Change-over contact, usable as NC or NO

Installation mode For mounting on DIN rail

Electric current

Max. power (cos phi 0,6) 3 A

Endurance

Electrical durability at nominal load in AC1 in operating cycles 50000

Texts

Type of connection With screw terminals

Voltage

Rated operational voltage Ue 230 - 230 V

Power

Power loss at full load 1 W

Settings

Programme cycles Programme cycle: 24 hours

Lighting

LED lamp power 450 W

Sustainability

RoHS conform Yes