




EE831



**Motion detector infrared 200°, IP55, wall mounted, anthracite**

**Technical Features**

**Detection**

Detection angle	200 - 200
Type of sensor	Movement detector

**Settings**

Time delay	5 S - 15 Min
------------	--------------

**Lighting**

Response brightness adjustable	5 - 1000 lx
--------------------------------	-------------

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Dimensions**

Width	83 mm
Recommended installation height	2.50 - 2.50 m

**Use conditions**

Operating temperature	-20 - 55 °C
-----------------------	-------------

**Materials**

Colour	Anthracite
Material	Plastic

**Safety**

Ingress Protection (IP) class	IP55
-------------------------------	------

**Installation, mounting**

Mounting on	Surface mounting
Suitable for outdoor usage	Yes

**Texts**

Function	Can be used as a single unit, main device or extension unit
Installation mode	For wall and ceiling mounting, corner installation with adapter
Type of connection	With plug-in terminals

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes