



VE112F

Enclosure,vector, IP55, 12M

Technical Features

Voltage

Nominal voltage	400 - 400 V
-----------------	-------------

Installation, mounting

Suitable for outdoor usage	No
Mounting on	Surface mounting

Electric current

Rated current	63 A
---------------	------

Equipment

Number of rails	1
Number of rows	1
Number of section in width	1
With lock	No
Has neutral terminal block	No

Capacity

Number of modules	12
-------------------	----

Functions

With conduit inlets	Yes
---------------------	-----

Dimensions

Height	302 mm
Width	310 mm
Depth	151 mm

Cover, door

Number of cabinet doors	1
Number of locks	0

Dimensions

Number of width units	12
-----------------------	----

Cover, door

Door/cover is transparent	Yes
Cabinet door type	Single door

Connection

Number of conduit inlets	12
--------------------------	----

Connectivity

Mounting type	Screw mounting
---------------	----------------

Materials

Material	Polystyrene (PS)
RAL code	7035
Colour	Light grey

Equipment

Has earthing terminal block	Yes
Has mounting plate	No

Materials

Ultraviolet-resistant	No
-----------------------	----

Safety

Protection class	Isolation class II
Impact resistance IK	IK08
Ingress Protection (IP) class	IP65

Safety

Locking type	Snap on lock Without lock
Glow wire test	750 °C
Protection class with door	IP65

Sustainability

RoHS conform	Yes
--------------	-----