




EE830



Motion detector infrared 200°, IP55, wall mounted, white

Technical Features

Detection

|                 |                   |
|-----------------|-------------------|
| Detection angle | 200 - 200         |
| Type of sensor  | Movement detector |

Settings

|            |              |
|------------|--------------|
| Time delay | 5 S - 15 Min |
|------------|--------------|

Lighting

|                                |             |
|--------------------------------|-------------|
| Response brightness adjustable | 5 - 1000 lx |
|--------------------------------|-------------|

Frequency

|           |            |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

Dimensions

|                                 |               |
|---------------------------------|---------------|
| Width                           | 83 mm         |
| Recommended installation height | 2.50 - 2.50 m |

Use conditions

|                       |             |
|-----------------------|-------------|
| Operating temperature | -20 - 55 °C |
|-----------------------|-------------|

Materials

|          |         |
|----------|---------|
| Colour   | White   |
| Material | Plastic |

Safety

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP55 |
|-------------------------------|------|

Installation, mounting

|                            |                  |
|----------------------------|------------------|
| Mounting on                | Surface mounting |
| Suitable for outdoor usage | Yes              |

Texts

|                    |                                                                 |
|--------------------|-----------------------------------------------------------------|
| Function           | Can be used as a single unit, main device or extension unit     |
| Installation mode  | For wall and ceiling mounting, corner installation with adapter |
| Type of connection | With plug-in terminals                                          |