



SK601

**Reverser 20 2F**

**Technical Features**

**Architecture**

Number of poles	2
Type of pole	2P

**Electric current**

Rated current	20 A
Rated conditional short-circuit current I <sub>cc</sub> with gl-gG fuses	8 kA

**Voltage**

Rated operational voltage U <sub>e</sub>	400 - 400 V
Type voltage supply	AC
Rated insulation voltage U <sub>i</sub>	690 V

**Capacity**

Number of modules	3
-------------------	---

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Frequency**

Frequency	50 - 50 Hz
-----------	------------

**Dimensions**

Height	85 mm
Width	53 mm
Depth	64 mm
Dimensions	85 x 53 mm

**Equipment**

Number of NO contacts	2
Number of NC contacts	2

**Use conditions**

Operating temperature	-10 - 40 °C
Storage/transport temperature	-40 - 80 °C

**Connection**

Cross-section flexible conductor	1.5 - 10 mm <sup>2</sup>
Cross-section rigid conductor	1 - 6 mm <sup>2</sup>

**Sustainability**

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes

Illustrations | Drawings

