




EE805A



Movement detector 360° flush mounted with normally open contact

Technical Features

Detection

Detection angle	360 - 360
Type of sensor	Movement detector Presence detector
Detection angle horizontal	360 - 360

Settings

Time delay	5 S - 30 Min
------------	--------------

Lighting

Response brightness adjustable	5 - 1000 lx
LED lamp power	400 W

Settings

Response sensitivity adjustable	No
---------------------------------	----

Lighting

Photocell sensitivity	5 - 1000 lx
-----------------------	-------------

Settings

Switch off delay time	0 s
Switch on delay time	0 s

Connection

Connector/plug type	Prism clamp
---------------------	-------------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Dimensions

Width	19 mm
Built-in depth	55 mm
Recommended installation height	2.5 - 3.5 m
Installation height	2 - 4 m

Use conditions

Operating temperature	-5 - 45 °C
-----------------------	------------

Materials

Colour	White
RAL code	9001
Material	Plastic
Surface finish	Matt

Safety

Ingress Protection (IP) class	IP21
-------------------------------	------

Installation, mounting

Mounting on	Flush mounting
Suitable for outdoor usage	No
Ceiling mounting possible	No

Texts

Function	Can only be used as individual unit
Installation mode	With spring clips for ceiling installation For ceiling mounting
Type of connection	With plug-in terminals

Power supply

Supply voltage	230 V +10%/-15%
----------------	-----------------

Reach distance	
Max. transmission range frontally	6 m
Max. transmission range sideways	6 m
Sustainability	
REACH-SVHC free	Yes
RoHS conform	Yes