



ST312

Safety transformer 25VA 230V/12-24V

Technical Features

Voltage

| | |
|------------------------------|-------------|
| Output voltage | 12 - 24 V |
| Output voltage 2 | 24 V |
| Rated operational voltage Ue | 230 - 230 V |
| Rated insulation voltage Ui | 4000 V |

Power

| | |
|----------------------|-------|
| Power consumption VA | 25 VA |
|----------------------|-------|

Frequency

| | |
|-----------|------------|
| Frequency | 50 - 50 Hz |
|-----------|------------|

Installation, mounting

| | |
|-------------|----------|
| Mounting on | DIN rail |
|-------------|----------|

Use conditions

| | |
|-----------------------|-------------|
| Operating temperature | -20 - 35 °C |
|-----------------------|-------------|

Capacity

| | |
|-------------------|---|
| Number of modules | 4 |
|-------------------|---|

Dimensions

| | |
|--------|-------|
| Height | 85 mm |
| Width | 70 mm |
| Depth | 58 mm |

Safety

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
| Temperature protection | Yes |

Equipment

| | |
|----------------------------|-----|
| Is short-circuit protected | Yes |
| On/off switch | No |

Connection

| | |
|----------------------------------|-------------------|
| Cross-section flexible conductor | 4 mm ² |
| Cross-section rigid conductor | 6 mm ² |

Sustainability

| | |
|-----------------|-----|
| Halogen free | Yes |
| REACH-SVHC free | Yes |
| RoHS conform | Yes |

Illustrations | Drawings

