



HNT250JR

### Moulded Case Circuit Breaker h3+ P250 LSI 3P3D 250A 40kA FTC

#### Technical Features

##### Electric current

|                                                                               |         |
|-------------------------------------------------------------------------------|---------|
| Rated current                                                                 | 250 A   |
| Rated ultimate short-circuit breaking capacity Icu under 230 V AC IEC 60947-2 | 50 kA   |
| Rated ultimate short-circuit breaking capacity Icu under 240 V AC IEC 60947-2 | 50 kA   |
| Rated ultimate short-circuit breaking capacity Icu under 400 V AC IEC 60947-2 | 40 kA   |
| Rated ultimate short-circuit breaking capacity Icu under 415 V AC IEC 60947-2 | 40 kA   |
| Breaking capacity on 1-pole for AC 230 V IEC 60947-2                          | 2.50 kA |
| Breaking capacity on 1-pole for AC 400 V IEC 60947-2                          | 2.50 kA |

##### Architecture

|                           |                 |
|---------------------------|-----------------|
| Number of poles           | 3               |
| Control/operation element | Toggle          |
| Device construction type  | Fixed built-in  |
| Neutral position          | Without neutral |

##### Electric current

|                                                                               |       |
|-------------------------------------------------------------------------------|-------|
| Rated ultimate short-circuit breaking capacity Icu under 690 V AC IEC 60947-2 | 6 kA  |
| Rated service breaking capacity Ics under 220 V AC according to IEC 60947-2   | 50 kA |
| Rated service breaking capacity Ics under 230 V AC according to IEC 60947-2   | 50 kA |
| Rated service breaking capacity Ics under 240 V AC according to IEC 60947-2   | 50 kA |
| Rated service breaking capacity Ics under 380 V AC according to IEC 60947-2   | 40 kA |
| Rated service breaking capacity Ics under 400 V AC according to IEC 60947-2   | 40 kA |
| Rated service breaking capacity Ics under 415 V AC according to IEC 60947-2   | 40 kA |
| Rated service breaking capacity Ics under 690 V AC according to IEC 60947-2   | 6 kA  |
| Rated current 10°C according to IEC 60947                                     | 250 A |
| Rated current 15°C according to IEC 60947                                     | 250 A |
| Rated current 20°C according to IEC 60947                                     | 250 A |
| Rated current 25°C according to IEC 60947                                     | 250 A |
| Rated current 30°C according to IEC 60947                                     | 250 A |
| Rated current at 35°C according to IEC 60947                                  | 250 A |
| Rated current at 40°C according to IEC 60947                                  | 250 A |
| Rated current 45°C according to IEC 60947                                     | 250 A |
| Rated current 50°C according to IEC 60947                                     | 250 A |
| Rated current 55°C according to IEC 60947                                     | 250 A |
| Rated current at 60°C according to IEC 60947                                  | 240 A |
| Rated current 70°C according to IEC 60947                                     | 200 A |
| Rated current 65°C according to IEC 60947                                     | 220 A |

##### Settings

|                                                           |                  |
|-----------------------------------------------------------|------------------|
| Ir1 current dial setting                                  | 90 A             |
|                                                           | 100 A            |
|                                                           | 110 A            |
|                                                           | 125 A            |
|                                                           | 140 A            |
|                                                           | 160 A            |
|                                                           | 180 A            |
|                                                           | 200 A            |
|                                                           | 225 A            |
|                                                           | 250 A            |
| Adjustment range short-term delayed short-circuit release | 122.9 - 2500.0 A |

##### Frequency

|           |            |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

##### Installation, mounting

|                               |            |
|-------------------------------|------------|
| Nominal tightening torque     | 12 - 12 Nm |
| Mounting-/Connection Position | Front      |

---

**Voltage**

|                                      |             |
|--------------------------------------|-------------|
| Rated impulse withstand voltage Uimp | 8000 V      |
| Rated insulation voltage Ui          | 800 V       |
| Rated operational voltage Ue         | 220 - 690 V |

---

**Functions**

|           |     |
|-----------|-----|
| Trip unit | LSI |
|-----------|-----|

---

**Power**

|                           |      |
|---------------------------|------|
| Total power loss under IN | 45 W |
| Power loss per pole at In | 15 W |

---

**Endurance**

|                                        |       |
|----------------------------------------|-------|
| Electric endurance in number of cycles | 10000 |
| Number of mechanical operations        | 40000 |

---

**Equipment**

|                                                         |   |
|---------------------------------------------------------|---|
| Number of auxiliary contacts as change-over contact     | 0 |
| Number of auxiliary contacts as normally closed contact | 0 |
| Number of auxiliary contacts as normally open contact   | 0 |

---

**Safety**

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP4X |
|-------------------------------|------|

---

**Use conditions**

|                       |             |
|-----------------------|-------------|
| Operating temperature | -25 - 70 °C |
|-----------------------|-------------|

---

**Connection**

|                                  |                          |
|----------------------------------|--------------------------|
| Cross-section flexible conductor | 35 - 150 mm <sup>2</sup> |
|----------------------------------|--------------------------|

---

**Cover, door**

|               |     |
|---------------|-----|
| Interlockable | Yes |
|---------------|-----|

---

**Connection**

|                               |                          |
|-------------------------------|--------------------------|
| Cross-section rigid conductor | 35 - 185 mm <sup>2</sup> |
| Connector/plug type           | Terminal                 |

---

**Cable**

|                |                     |
|----------------|---------------------|
| Cable material | Copper<br>Aluminium |
|----------------|---------------------|

---

**Use conditions**

|                                                          |   |
|----------------------------------------------------------|---|
| Degree of pollution according to IEC 60664 / IEC 60947-2 | 3 |
|----------------------------------------------------------|---|

---

**Dimensions**

|        |        |
|--------|--------|
| Height | 165 mm |
| Width  | 105 mm |
| Depth  | 97 mm  |

---

**Controls and indicators**

|                        |    |
|------------------------|----|
| Motor drive integrated | No |
|------------------------|----|

---

**Compatibility**

|                                 |     |
|---------------------------------|-----|
| Suitable for DIN Rail           | No  |
| Compatible with RDC AOB         | No  |
| Suitable for distribution board | Yes |

---

**Power supply**

|                       |               |
|-----------------------|---------------|
| Position power supply | Bidirectional |
|-----------------------|---------------|

**Electrical protection**

|                                                         |        |
|---------------------------------------------------------|--------|
| Long-time overload protection (ltd): delay (tr)         | 0.5 s  |
|                                                         | 1.5 s  |
|                                                         | 2.5 s  |
|                                                         | 5 s    |
|                                                         | 7.5 s  |
|                                                         | 9 s    |
|                                                         | 10 s   |
|                                                         | 12 s   |
|                                                         | 14 s   |
|                                                         | 16 s   |
|                                                         |        |
| Short-time protection (std): current (lsd)              | 1.5    |
|                                                         | 2      |
|                                                         | 3      |
|                                                         | 4      |
|                                                         | 5      |
|                                                         | 6      |
|                                                         | 7      |
|                                                         | 8      |
|                                                         | 10     |
|                                                         |        |
| Short-time protection (std): delay (tsd)                | 50 ms  |
|                                                         | 100 ms |
|                                                         | 200 ms |
|                                                         | 300 ms |
|                                                         | 400 ms |
| Instantaneous protection (li): dial setting coefficient | 3      |
|                                                         | 4      |
|                                                         | 5      |
|                                                         | 6      |
|                                                         | 7      |
|                                                         | 8      |
|                                                         | 9      |
|                                                         | 10     |
|                                                         | 11     |
|                                                         |        |

**Sustainability**

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|