




EE804A



**Movement detector 360° surface mounted with normally open contact**

**Technical Features**

**Detection**

Detection angle	360 - 360
Type of sensor	Movement detector Presence detector
Detection angle horizontal	360 - 360

**Settings**

Time delay	5 S - 30 Min
------------	--------------

**Lighting**

Response brightness adjustable	5 - 1000 lx
LED lamp power	400 W

**Settings**

Response sensitivity adjustable	No
---------------------------------	----

**Lighting**

Photocell sensitivity	5 - 1000 lx
-----------------------	-------------

**Settings**

Switch off delay time	0 s
Switch on delay time	0 s

**Connection**

Connector/plug type	Screw terminal
---------------------	----------------

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Dimensions**

Width	105.50 mm
Built-in depth	0 mm
Recommended installation height	2.5 - 3.5 m
Installation height	2 - 4 m

**Use conditions**

Operating temperature	-5 - 45 °C
-----------------------	------------

**Materials**

Colour	White
Material	Plastic
Surface finish	Matt

**Safety**

Ingress Protection (IP) class	IP21
-------------------------------	------

**Installation, mounting**

Mounting on	Surface mounting
Suitable for outdoor usage	No
Ceiling mounting possible	Yes

**Texts**

Function	Can only be used as individual unit
Installation mode	Installation possible on flush-mounted box For ceiling mounting
Type of connection	With screw terminals

**Power supply**

Supply voltage	230 V +10%/-15%
----------------	-----------------

**Reach distance**

Max. transmission range frontally	6 m
Max. transmission range sideways	6 m

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes